


REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
D	08/20/02	ADDED .26 (7) DIMENSION (ZONE B-7)	7832	RGL	--



NOTES:

- MATERIAL:
- CONNECTOR:
HIGH CONDUCTIVITY COPPER ALLOY, CONDUCTIVITY 85% IACS MINIMUM.
SURFACE SILVER ELECTROPLATE, .0005 NOMINAL THICKNESS (F70H2C)
- BOLTS, SILICON BRONZE
- NUTS, NON-MAGNETIC STAINLESS STEEL
- DIMENSIONS IN BRACKETS () DENOTES METRIC UNITS (SI UNITS) AND ARE ROUNDED TO THE NEAREST WHOLE NUMBER. UNLESS OTHERWISE SPECIFIED THESE UNITS SHALL BE USED FOR REFERENCE ONLY.
- 5/8 BOLTS ARE THREADED THE FULL LENGTH.

FOR GENERAL ELECTRIC POWER SYSTEM ONLY

TO ORDER BURNDY PRODUCTS CALL 1-800-348-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.burndy.com>

STUD CONNECTOR

ITEM NO: 26002097		
CAT NO: FD80G11SV		
SCALE: 3:10	DRAWN BY: LAVOIE 08/02/01	DRAWING NO WSD213725-01 SHEET 1 OF 1
CHECKER: J LETOURNEAU 08/14/01	DSN APPVL: TRR/GD 08/06/01	
MFG APPVL: -- 01/01/01	QC APPVL: J BRODEUR 08/06/01	REV D
MKT APPVL: D HAMILTON 08/06/01	PROD FAM: SUBSTATION	
PROJECT: SUBSTATION	SIZE: D	
DOCUMENT TYPE: --	REL LEVEL: Released	

REV: PE0200

7/8-9 UNC X 6.50 LG SILICON BRONZE BOLT WITH 7/8-9 UNC NON-MAGNETIC STAINLESS STEEL NYLOK SELF LOCKING NUT 6X

5/8-11 UNC X 3.25 LG SILICON BRONZE BOLT WITH 5/8-11 UNC NON-MAGNETIC STAINLESS STEEL NYLOK SELF LOCKING NUT 12X

SCALE 4:5