


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	05/04/2016	NOTE 2 AND 3 ADDED	38590	SM	MB



NOTES:

- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE CURRENT RATING OF 800 AMPS. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

3 UL LISTED TO UL 467 GROUNDING & BONDING STANDARD, FILE E9999.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: 50071542	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: B2G10D75G150SV	
CANADA:		DRAWN BY: G. RUGGIERO 04-28-2016	
1-800-361-6975 (QUEBEC)		CHECKER: L. TROMBLEY 04-28-2016	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: L. TROMBLEY 04-28-2016	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		MFG APRVL: M. STEVENS 04-28-2016	
		QA APRVL: C. LINDQUIST 04-28-2016	
		MKT APRVL: J. HOGAN 04-28-2016	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: FOCUS	SIZE	50071543	B
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			