


NOTES:

1. DIMENSIONS SUBJECT TO +/- 5% TOLERANCE
2. LEAKAGE DISTANCE - 782 mm
3. ALTITUDE 0-3600 m ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 5.9 kg
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE U_c 19.5 kV
6. RATED VOLTAGE U_r 24 kV RMS



10 kA STEEP CURRENT I_{res}	500 A SWITCHING SURGE I_{res} kV	MAXIMUM 8/20 RESIDUAL VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5.0 kA	10 kA	20 kA	40 kA
74.3	52.3	56.3	59.0	61.9	64.6	72.5	81.5

IEC CLASS 2 SURGE ARRESTER	 POWER SYSTEMS	HUBBELL® POWER SYSTEMS				
		TITLE PVI-LP ARRESTER 19.5 kV U _c				
	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE S	DWG NO. --	CAT / PART / ASSY NO. 214520-C2BC		REV 0
REV DATE 07/27/2023	DO NOT SCALE THIS DRAWING		DRN BY RVK		DATE 07/27/23	SHEET 1 OF 1