




CATALOG NUMBER	ITEM NUMBER	ACCOMMODATES	MARKINGS
FD645C5	296286	7/8-12UN	BURNDY FD645C5 (7/8-12)
FD645C5T14	25018834	7/8-14UNF	BURNDY FD645C5T14 (7/8-14)

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	08/08/2016	FOCUS REQUEST FPN1607054	44574	CV	MB



NOTES:

- 1 MATERIAL:
COPPER ALLOY.
- 2 ACCOMMODATES:
SEE TABLE.
- 3 NOMINAL BOLT INSTALLATION TORQUE:
3/8" HEX. SILICON BRONZE HARDWARE 240 IN-LBS [28 Nm]
- 4 DIMENSIONS IN BRACKETS [] DENOTES METRIC UNITS [SI UNITS]
AND ARE ROUNDED TO THE NEAREST WHOLE NUMBER. UNLESS
OTHERWISE SPECIFIED THESE UNITS SHALL BE USED FOR
REFERENCE ONLY.
- 5 THE CONCEPT SHOWN INCORPORATES PRINCIPLES WHICH PERMIT OPERATION
AT A VOLTAGE GRADIENT NORMALLY ASSOCIATED WITH 138 KV RMS
OPERATION PHASE TO PHASE.
- 6 HEX BOLTS CAPTURED TO PREVENT TURNING DURING INSTALLATION.
- 7 MARKING:
BURNDY
FD645C5T14
7/8"-14 STUD.

TO ORDER BURNDY® PRODUCTS CALL		STUD CONNECTOR	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE CAT. NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: VIMAL C 8/8/2016 CHECKER: MANIKANDAN B 8/8/2016	
FOR PRODUCT INFO: http://www.burndy.com		DSN APRVL: -- MFG APRVL: -- QA APRVL: -- MKT APRVL: -- PROD FAM: --	
			
		DRAWING NO	
		50074852	
		REV	
		A	
		SHEET 1 OF 1	