


NOTES:

1. DIMENSIONS SUBJECT TO +/- 5% TOLERANCE
2. LEAKAGE DISTANCE (mm) - 1173
3. ALTITUDE 0-3600 m ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 6.2 kg.
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE U_c 24.4 kV
6. RATED VOLTAGE U_r 30 kV RMS.



10 kA STEEP CURRENT U_{res} kV	500 A SWITCHING SURGE U_{res} kV	MAXIMUM 8/20 RESIDUAL VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
93.4	65.3	70.3	73.8	77.3	80.7	90.6	101.8

10 kA ARRESTER IEC 60099-4 Ed2.2 CLASS 2 IEC 60099-4 Ed3.0 CLASS STATION LOW	 HUBBELL® POWER SYSTEMS	TITLE PVI-LP ARRESTER 24.4 kV Uc			
	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE S	DWG NO. --	CAT / PART / ASSY NO. 214524-C2CC	REV 0
REV DATE 12/04/20	DO NOT SCALE THIS DRAWING		DRN BY RVK	DATE 12/04/20	SHEET 1 OF 1