


NOTES:

1. DIMENSIONS SUBJECT TO +/- 5% TOLERANCE
2. LEAKAGE DISTANCE (mm) - 1173
3. ALTITUDE 0-3600 m ABOVE SEA LEVEL
4. WEIGHT OF UNIT INCLUDING HARDWARE - 6.2 kg.
5. MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE U_c 29.0 kV
6. RATED VOLTAGE U_r 36 kV RMS.



10 kA STEEP CURRENT I_{res} kV	500 A SWITCHING SURGE I_{res} kV	MAXIMUM 8/20 RESIDUAL VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
111.3	78.4	84.4	88.6	92.8	96.9	108.8	122.2

10 kA
ARRESTER
IEC 60099-4 Ed2.2
CLASS 2
IEC 60099-4 Ed3.0
CLASS STATION LOW

CONFIDENTIAL: THIS DRAWING AND ITS
CONTENTS ARE CONFIDENTIAL AND THE
EXCLUSIVE PROPERTY OF HUBBELL
POWER SYSTEMS. NO PUBLICATION,
DISTRIBUTION OR COPIES MAY BE MADE
WITHOUT THE WRITTEN CONSENT OF
HUBBELL POWER SYSTEMS.
HUBBELL POWER SYSTEMS UNPUBLISHED
ALL RIGHTS RESERVED UNDER THE
COPYRIGHT LAWS.



HUBBELL® POWER SYSTEMS

TITLE
PVI-LP ARRESTER
29.0 kV U_c

SIZE S	DWG NO. --	CAT / PART / ASSY NO. 214529-C2CC	REV 0
-----------	---------------	--------------------------------------	----------

DO NOT SCALE THIS DRAWING	DRN BY RVK	DATE 12/04/20	SHEET 1 OF 1
------------------------------	------------	---------------	--------------

REV DATE
12/04/20