

600 A 35 kV 3-Position Deadbreak Junction

Conforms to all Requirements of IEEE Std. 386 - Latest Revision

Ratings

Maximum Continuous Voltage.....21.1 kV Phase-to-Ground
Continuous Current.....600 A
Overload Current 4 hour rating.....900 A

Short-Time Current Ratings



0.17 Sec. Duration.....25,000 A rms Symmetrical
3.00 Sec. Duration.....10,000 A rms Symmetrical

Insulation Withstand Voltages

Basic Impulse Level.....150 kV Crest (1.2 x 50 µSec. wave)
60 Hz (60 Sec.).....50 kV rms
Partial Discharge Extinction Voltage (5 pC).....26 kV rms

Production Tests

100% factory tested for Partial Discharge and either AC 60 Hz (45 kV for 60 Sec.) or Impulse (BIL) (125 kV 1.2 x 50 µSec. wave).



REV DATE
2/5/2019

CONTENTS ARE CONFIDENTIAL AND THE
EXCLUSIVE PROPERTY OF HUBBELL
POWER SYSTEMS. NO PUBLICATION,
DISTRIBUTION OR COPIES MAY BE MADE
WITHOUT THE WRITTEN CONSENT OF
HUBBELL POWER SYSTEMS.
HUBBELL POWER SYSTEMS UNPUBLISHED
ALL RIGHTS RESERVED UNDER THE
COPYRIGHT LAWS.



HUBBELL POWER SYSTEMS, Inc.

TITLE
600 A 35 kV 3-POSITION
DEADBREAK-JUNCTION / BRACKET

SIZE SB	DWG NO. --	CAT / PART / ASSY NO. 635J3B	REV 0
DO NOT SCALE THIS DRAWING	DRN BY BvB	DATE 2/5/2019	SHEET 1 OF 1