


CLAMP TYPE LINE & GROUND TERMINALS
SUITABLE FOR USE WITH CU OR AL
CONDUCTOR .25(6) TO .81(21) DIA



- NOTES:
- 1 PACKED FOR DOMESTIC SHIPMENT
 - 2 DIMENSIONS SUBJECT TO ±3% TOLERANCE.
 - 3 DIMENSIONS ARE IN INCHES(MM).
 - 4 ALTITUDE 0 TO 12,000 FT(3600 METERS) ABOVE SEA LEVEL.
 - 5 PRESSURE RELIEF 40 KA RMS.
 - 6 LEAKAGE DISTANCE - 30.8 IN(782 MM).
 - 7 WEIGHT - 10 LB(5 KG).
 - 8 MAXIMUM CONTINUOUS LINE-TO-GROUND OPERATING VOLTAGE RATING - 17 KV MCOV.
 - 9 DUTY CYCLE VOLTAGE RATING - 21 KV RMS.
 - 10 DARK GRAY WEATHERSHEDS.

.5 μ SEC 10KA IR kV	500 A SWITCHING SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
62.4	43.5	46.9	49.2	51.5	53.8	60.4	67.8

INTERMEDIATE
CLASS
ARRESTER

Program Revision
2021.04.27.03.52.46

REV DATE
08/04/04

HUBBELL/BRASS
TOLERANCE CHART

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

HUBBELL® POWER SYSTEMS

TITLE
**PVI-LP ARRESTER
17 KV MCOV**

SIZE S	DWG NO. ISPOLY-IN	CAT / PART / ASSY NO. 300817-3001	REV 2
DO NOT SCALE THIS DRAWING	DRN BY NDN	DATE 11/26/02	SHEET 1 OF 1