


REV	DATE	DESCRIPTION	ECO	BY	CHK
H	07/29/2020	UPDATED TABLE DATA	53958	JL	TR



NOTES:

1. APPROXIMATE AMP RATING: 300A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.


3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

4 ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	BRAID		
	ITEM NO: SEE TABLE		
	CAT. NO: BB100L--G21TN (SEE TABLE)		
	DRAWN BY: E.MARTIN	5/21/2012	BURNDY®
	CHECKER: TROY	6/7/2013	
	DSN APRVL: --		
	MFG APRVL: LOGAN	6/7/2013	
	QA APRVL: JOE	6/11/2013	
	MKT APRVL: KATHLEEN	6/7/2013	
	PROD FAM: BRAID	DRAWING NO	
PROJECT #: FPN1601032	SIZE	50002016	
DOCUMENT TYPE: SALES	B	H	
REL LEVEL: WorkInProgress		SHEET 1 OF 2	

ITEM NUMBER	CATALOG NO.	L	L1
50067315	BB100L8D87G21TN	7.87 [200]	8.87 [225]
50002012	BB100L12D80G21TN	11.80 [300]	12.80 [325]
50080687	BB100L16D75G21TN	15.75 [400]	16.75 [425]
50002013	BB100L18D70G21TN	17.70 [450]	18.70 [475]
50058309	BB100L20D69G21TN	19.69 [500]	20.69 [525]
50025608	BB100L24D60G21TN	23.60 [599]	24.60 [625]
50058310	BB100L26D59G21TN	25.59 [650]	26.59 [675]
50058311	BB100L28D56G21TN	27.56 [700]	28.56 [725]
50063435	BB100L30D53G21TN	29.53 [750]	30.53 [775]
50002014	BB100L32D48G21TN	31.48 [800]	32.48 [825]
50049170	BB100L34D46G21TN	33.46 [850]	34.46 [875]
50080688	BB100L36D43G21TN	35.43 [900]	36.43 [925]
50049171	BB100L40D37G21TN	39.37 [1000]	40.37 [1025]
50063442	BB100L45D02G21TN	44.02 [1118]	45.02 [1144]
50049172	BB100L48D24G21TN	47.24 [1200]	48.24 [1225]
50063436	BB100L52D18G21TN	51.18 [1300]	52.18 [1325]
50063437	BB100L56D12G21TN	55.00 [1397]	56.00 [1422]
50063438	BB100L59G21TN	58.00 [1473]	59.00 [1499]
50002015	BB100L60G21TN	59.00 [1499]	60.00 [1524]
50063439	BB100L79D74G21TN	78.74 [2000]	79.74 [2025]
50049173	BB100L95D49G21TN	94.49 [2400]	95.49 [2425]
50049174	BB100L103D36G21TN	102.36 [2600]	103.36 [2625]
50063440	BB100L126D98G21TN	125.98 [3200]	126.98 [3225]
50063441	BB100L134G21TN	133.00 [3378]	134.00 [3404]
50049169	BB100L142D73G21TN	141.73 [3600]	142.73 [3625]
50114415	BB100179D13G21TN	178.13 [4524]	179.13 [4549]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
H	07/29/2020	UPDATED TABLE DATA	53958	JL	TR

<p>TO ORDER BURNDY® PRODUCTS CALL</p> <p>UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)</p> <p>CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)</p> <p>FOR PRODUCT INFO: http://www.burndy.com</p>	BRAID		
	ITEM NO: SEE TABLE		
	CAT. NO: BB100L--G21TN (SEE TABLE)		
	DRAWN BY: E.MARTIN	5/21/2012	
	CHECKER: TROY	6/7/2013	
	DSN APRVL: --		
	MFG APRVL: LOGAN	6/7/2013	
	QA APRVL: JOE	6/11/2013	
	MKT APRVL: KATHLEEN	6/7/2013	
	PROD FAM: BRAID	DRAWING NO	REV
PROJECT #: FPN1601032	SIZE	50002016	
DOCUMENT TYPE: SALES	B	H	
REL LEVEL: WorkInProgress		SHEET 2 OF 2	