


REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	02/06/13	UPDATE NOTE PER M/U.	30266	RB	PW

CUTTING CAPACITY
DO NOT CUT OR ENERGIZED LINE
CU - 600 KCMIL
AL - 600 KCMIL
MAX INSUL. DIA. - 1.31 IN. [33]



NOTES:

READ AND FOLLOW ALL INSTRUCTIONS PROVIDED BY THE OPERATOR'S MANUAL AND WARNING LABELS BEFORE USING THIS TOOL.
DIMENSIONS IN [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED. METRIC DIMENSIONS ARE FOR REFERENCE ONLY.

SPECIFICATIONS:

WEIGHT: 3.5 LBS. [1.5 KG].

JAWS:

PATENTED HIGH STRENGTH STEEL, AND REPLACEABLE. (CAT. NO.: MCC600BLADESET. INCLUDES TWO BLADES), YIELDING MINIMUM CONDUCTOR DISTORTION.

HANDLES:

FIBERGLASS WITH COMFORT GRIP DESIGN AND ERGONOMIC HANDLE ENDS PROVIDE A POSITIVE ANTI-SLIP GRIP.

FIBERGLASS HANDLE MATERIAL MEETS OR EXCEEDS ASTM F711. (100 kV/ft. DIELECTRIC STRENGTH)

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		MANUAL CABLE CUTTER TOOL	
		ITEM NO: 50009948	
		CAT NO: MCC600	
		SCALE: NTS	BURNDY
		DRAWN BY: R. BOISVERT 10/17/12	
		CHECKER: P. WASON 10/19/12	
		DSN APPVL: P. WASON 10/15/12	
		MFG APPVL: S. GANYAW 10/17/12	
		QC APPVL: C. KOWALCZYK 10/17/12	
		MKT APPVL: -- --	DRAWING NO
		PROD FAM: --	50009950
		PROJECT #: --	SIZE
		DOCUMENT TYPE: Sales	D
		REL LEVEL: AutoCAD	SHEET 1 OF 1