




CAT. NO.	WIRE RANGE	STUD SIZE [METRIC SIZE]	3 HYDRAULIC TOOLING					DIELESS TOOLING	NO. CRIMPS	WIRE STRIP LENGTH	REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
			DIE INDEX	TOOL CAT. NO.							B	8/19/2014	UPDATED AS PER MARKUP			37422
YAD30M20E34	250-300 Kcmil STR.CU CODE & FLEX [120-150]mm²	3/4" [19]	----	3 Y46, PAT46			Y750, PAT750		Y81KFT- SERIES PAT81KFT- SERIES Y4PC834- SERIES PAT4PC834- SERIES	1	1-1/8"					
				ADAPTOR	NEST	INDENTOR	NEST	INDENTOR								
				---	P44D	P48PR2	UM30N	UME								
				PUADP1	UM30N	UME										



- NOTES:
1. MATERIAL: COPPER.
 2. FINISH: TIN PLATED.
 3. Y35P3 ADAPTOR REQUIRED FOR P48PR2 INDENTORS IN Y46 AND PAT46 TOOLS.
 4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY PRODUCTS CALL				NON-INSULATED BRAZED BARREL COPPER TERMINAL			
UNITED STATES				ITEM NO: 50002503			
1-800-346-4175 (LONDONDERRY, NH)				CAT. NO: YAD30M20E34			
CANADA:				DRAWN BY: T.BALAN	10/30/2012		
1-800-361-6975 (QUEBEC)				CHECKER: M.JEFF	11/29/2012		
1-800-387-6487 (ALL OTHER PROVINCES)				DSN APRVL: M.JEFF	11/29/2012		
FOR PRODUCT INFO: http://www.burndy.com				MFG APRVL: K.CHERYL	11/29/2012		
				MKT APRVL: G.STEWART	11/28/2012		
PROD FAM:		SIZE		DRAWING NO		REV	
PROJECT #:		B		50013666		B	
DOCUMENT TYPE: Sales				SHEET 1 OF 1			
REL LEVEL: Released							