




DRY ARCING DISTANCE _ _ _ _ _ 566 MM (22.3 IN)
 LEAKAGE DISTANCE _ _ _ _ _ 1478 MM (58.2 IN)
 60 Hz DRY FLASHOVER _ _ _ _ _ 230 kV
 60 Hz WET FLASHOVER _ _ _ _ _ 180 kV
 IMPULSE POS. CRITICAL FLASHOVER _ _ _ 360 kV
 IMPULSE POS. WITHSTAND _ _ _ _ _ 330 kV
 SCL _ _ _ _ _ 11 kN (2470 LB.)
 RCL _ _ _ _ _ 5.5 kN (1235 LB.)
 NET WEIGHT _ _ _ _ _ 7.8 KG (17.1 LB.)

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.				HUBBELL® POWER SYSTEMS	
		TITLE VERI LITE 69 KV LINE POST			
REV DATE	06/21/11	SIZE	DWG NO.	CAT / PART / ASSY NO.	REV
		S	--	80S069-0F00	2
DO NOT SCALE THIS DRAWING		DRN BY JVR		DATE 05/16/06	SHEET 1 OF 1