


CATALOG NUMBER	NO. OF CIRCUITS	PART CATALOG NUMBER	DESCRIPTION	QTY
RK1492	2	RK149A	PHENOLIC TERMINAL BLOCK, 30 AMP, 2 CIRCUITS, (2) #8-32 X 5/16" LG, BRASS, NICKEL PLATED, BINDING HEAD SCREWS, #10 MOUNTING STUD HOLES.	1
		RKBAG35X3	POLY-BAG CLEAR RED/WHITE	
RK2252	6	RK225A	PHENOLIC TERMINAL BLOCK, 30 AMP, 6 CIRCUITS, (6) #8-32 X 5/16" LG, BRASS, NICKEL PLATED, BINDING HEAD SCREWS, #10 MOUNTING STUD HOLES.	1
		RKBAG4X5	POLY-BAG CLEAR RED/WHITE	
RK1512	8	RK151A	PHENOLIC TERMINAL BLOCK, 30 AMP, 8 CIRCUITS, (8) #8-32 X 5/16" LG, BRASS, NICKEL PLATED, BINDING HEAD SCREWS, #10 MOUNTING STUD HOLES.	1
		RKBAG4X8	POLY-BAG CLEAR RED/WHITE	
RK1522	10	RK152A	PHENOLIC TERMINAL BLOCK, 30 AMP, 10 CIRCUITS, (10) #8-32 X 5/16" LG, BRASS, NICKEL PLATED, BINDING HEAD SCREWS, #10 MOUNTING STUD HOLES.	1
		RKBAG4X8	POLY-BAG CLEAR RED/WHITE	
RK2262	12	RK226A	PHENOLIC TERMINAL BLOCK, 30 AMP, 12 CIRCUITS, (12) #8-32 X 5/16" LG, BRASS, NICKEL PLATED, BINDING HEAD SCREWS, #10 MOUNTING STUD HOLES.	1
		RKBAG4X8	POLY-BAG CLEAR RED/WHITE	
RK1532	14	RK153A	PHENOLIC TERMINAL BLOCK, 30 AMP, 14 CIRCUITS, (14) #8-32 X 5/16" LG, BRASS, NICKEL PLATED, BINDING HEAD SCREWS, #10 MOUNTING STUD HOLES.	1
		RKBAG4X1225	POLY-BAG CLEAR RED/WHITE	
RK2272	16	RK227A	PHENOLIC TERMINAL BLOCK, 30 AMP, 16 CIRCUITS, (16) #8-32 X 5/16" LG, BRASS, NICKEL PLATED, BINDING HEAD SCREWS, #10 MOUNTING STUD HOLES.	1
		RKBAG4X1225	POLY-BAG CLEAR RED/WHITE	

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/04/2012	SALES DRAWING CREATION	29581	PM	MB



TO ORDER BURNDY® PRODUCTS CALL		CIRCUIT TERMINAL BLOCK			
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A			
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE			
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: PALANI M 12/04/2012			
		CHECKER: --			
		DSN APRVL: --		MFG APRVL: FRED 07/24/2013	
		QA APRVL: --		MKT APRVL: ROBBIN 07/23/2013	
		PROD FAM: --		DRAWING NO	
		PROJECT #: --		50015437	
		DOCUMENT TYPE: SALES		REL LEVEL: Released	
		SIZE: B		SHEET 1 OF 1	
				REV: A	