



SL. NO.	CATALOG NUMBER	ITEM NUMBER
1	BG18G36TN	332672
2	BG18G36W	33288V



REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	05/28/2013	SALES DRAWING CREATION	31814	PM	MB



NOTES:

1. APPROXIMATE AMP RATING: 415 INDOOR, 495 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

- 3 SUFFIX 'TN' DENOTES ELECTRO-TIN PLATED FERRULES.
- 4 SUFFIX 'W' DENOTES HOT TIN DIPPED FERRULES.
- 5 LISTED TO UL467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		<b>BRAID JUMPER</b>	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: PALANI M 05/22/2013	
		CHECKER: TROY 06/04/2013	
		DSN APRVL: --	
		MFG APRVL: LOGAN 06/05/2013	
		QA APRVL: JOE 06/04/2013	
		MKT APRVL: KATHLEEN 06/04/2013	
		PROD FAM: MECHANICAL GROUNDING	
		DRAWING NO	
		50025657	
		REV	
		A	
		SHEET 1 OF 1	