


CATALOG NO.	CONDUCTOR		INSTALLATION TOOLING (# CRIMPS)								
			COLOR CODE	DIE INDEX	TYPE	MECHANICAL	HYDRAULIC			DIELESS (# CRIMPS)	WIRE STRIP LENGTH
	MD6, OUR840, MD7-34R	BCT500HS, Y500CTHS				Y35, Y39 Y750, PAT750	3 Y46				
YA26LNT875MMSL	2/0 AWG CLASS B & C	70	BLACK	13	2	W26VT (2) W26RT (2) X26RT (2)	X26RT (2) W26VT (2) W26RT (2)	U26RT (1)	U26RT (1)	MY29-3 (1) MY29-11 (1) MRC840 Y644HSXT (1) Y81KFT (1) Y81KFTMBH (1) PAT81KFT-18V (1)	1"

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	05/25/2015	SALES DRAWING RELEASED	40385	ARJ	BT



NOTES:

1. MATERIAL: COPPER TUBING
2. FINISH: TIN PLATED.
3. CAT NO. PUADP-1 ADAPTOR IS REQUIRED TO USE 'U' DIES IN Y46 SERIES TOOLS.
4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
5. APPROXIMATE WEIGHT: .073 LBS

TO ORDER BURNDY PRODUCTS CALL		HYLUG™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 10083618	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: YA26LNT875MMSL	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: SENTILVEL 04/02/2015	
		CHECKER: MANIKANDAN 04/02/2015	
		DSN APRVL: --	
		MFG APRVL: --	
		QA APRVL: --	
		MKT APRVL: --	
PROD FAM: CM&R COMPRESSION		DRAWING NO	REV
PROJECT #: --		50057848	A
DOCUMENT TYPE: SALES		SIZE	
REL LEVEL: Released		B	
		SHEET 1 OF 1	