


CATALOG NUMBER	LENGTH "L"	APPROXIMATE WEIGHT
BD24GTN	24.00 [610]	3.262 LBS
BD36GTN	36.00 [914]	5.256 LBS
BD48GTN	48.00 [1219]	7.250 LBS
BD60GTN	60.00 [1524]	9.244 LBS

REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	10/06/2016	DRAWING RELEASED	45023	CV	MB



NOTES:

- APPROXIMATE AMP. RATING : 190 INDOOR , 225 OUTDDOR.
THIS RATING MAY VARY WITH AMBIENT CONDITIONS.
ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- CAN BE ORDERED WITH PLATED FERRULES BY ADDING A SUFFIX AS SHOWN BELOW:
"NK" - FOR NICKEL PLATING
"SV" - FOR SILVER PLATING
"TN" - FOR TIN PLATING
"W" - FOR HOT TIN DIPPED
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- COVERED WITH GREEN HEAT SHRINK.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	BRAID			
	ITEM NO: N/A			
	CAT. NO: SEE TABLE			
	DRAWN BY: AVINASH	8/7/2015		
	CHECKER: MANIKANDAN B	8/7/2015		
DSN APRVL: --				
MFG APRVL: --				
QA APRVL: --				
MKT APRVL: --				
PROD FAM: --				
PROJECT #: FOCUS	SIZE	DRAWING NO	REV	
DOCUMENT TYPE: SALES		50060399	A	
REL LEVEL: WorkInProgress	B	SHEET 1 OF 1		