





PCORE
ELECTRIC


DATE	1-3-05	REV. DATE	8-22-12
MAXIMUM ALTITUDE	10000 ft [3000 m]		
NET WEIGHT	175 lb [79 kg]		
ANGLE OF INCLINATION FROM THE VERTICAL	0° TO 60°		

kV CLASS	34.5 kV	BIL	200 kV	Uy	22 kV
CURRENT RATING					
4000 AMP BOTTOM CONNECTED					
MIN. CREEP	40.00 [1016.0]	MIN. STRIKE	18.00 [457.2]		
CREEP/Uy	1.82 [46.2]	STD.	IEEE C57.19.00/01		
PCB CONTENT OF OIL IS LESS THAN 1 ppm					

DWG.	CATALOG NUMBER	GLAZE COLOR
SD	B-88843-9	BROWN
SD	B-88843-9-70	LT. GRAY
TITLE		
POC BUSHING		
EXTRA LONG UPPER PORCELAIN		



MOUNTING FLANGE DETAIL



FLANGE ALIGNMENT DIAGRAM
TOP VIEW

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION	"EXTRA LONG UPPER PORCELAIN" WAS "HIGH ALTITUDE"	SCALE	1/5
----------	--	-------	-----

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER