


NOTES:

1. MATERIAL:
 BODY - GALV. FORGED STEEL
 BOLT, JAM NUT, CLEVIS PIN - GALV. STEEL.
 COTTER PIN - STAINLESS STEEL
2. GALVANIZING PER ASTM A153



| | | | | | | | | | | | | | |
|--------------------------------------|------------|-----------------------|--------------|--|--|------------|--------------|-----------------------|-----|---|----------|------------|---|
| -- | --- | -- | -- | ANDERSON* | HUBBELL® POWER SYSTEMS | | | | | | | | |
| EC # | DATE | CHG BY | RESP ENG | | ANCHOR SHACKLE ASSEMBLY | | | | | | | | |
| DESC OF DWG: -- -- -- -- | | | | CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. | TITLE | | | | | | | | |
| REASON (S) FOR CHANGE: -- | | | | | <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 10%;">SIZE</td> <td style="width: 20%;">DWG NO.</td> <td style="width: 40%;">CAT / PART / ASSY NO.</td> <td style="width: 30%;">REV</td> </tr> <tr> <td style="text-align: center;">B</td> <td style="text-align: center;">CUTSHEET</td> <td style="text-align: center;">97415-3002</td> <td style="text-align: center;">A</td> </tr> </table> | SIZE | DWG NO. | CAT / PART / ASSY NO. | REV | B | CUTSHEET | 97415-3002 | A |
| SIZE | DWG NO. | CAT / PART / ASSY NO. | REV | | | | | | | | | | |
| B | CUTSHEET | 97415-3002 | A | | | | | | | | | | |
| DISPOSITION OF MAT'L: -- | | | | <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 20%;">DO NOT SCALE THIS DRAWING</td> <td style="width: 20%;">DRN BY JEB</td> <td style="width: 20%;">DATE 6/10/86</td> <td style="width: 40%;">SHEET 1 OF 1</td> </tr> </table> | DO NOT SCALE THIS DRAWING | DRN BY JEB | DATE 6/10/86 | SHEET 1 OF 1 | | | | | |
| DO NOT SCALE THIS DRAWING | DRN BY JEB | DATE 6/10/86 | SHEET 1 OF 1 | | | | | | | | | | |