





4

3

2

1

ITEM NO.	DESCRIPTION	QTY.
1	POLE MOUNT BRACKET	2
2	U-BOLT	2
3	M6 WASHER	4
4	M6 HEX NUT	4
5	NUT	1
6	STUD	1
7	ATS-200 CABLE	4
8	RPSMA PLUG	4



UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES(MM). TOLERANCES: ANGULAR: MACH±1° BEND ±1° .XX = ±.01 (.25) .XXX = ±.005 (.127)		NAME	DATE
INTERPRET GEOMETRIC TOLERANCING PER: ASME Y14.5M-2018		DRAWN	MA 1/5/2024
PROJECT REF: 203-23		CHECKED	IA 1/5/2024
MATERIAL: MULTIPLE		ENG APPR.	NM 1/5/2024
FINISH: NA		MFG APPR.	
DO NOT SCALE DRAWING		COMMENTS:	



PROPRIETARY AND CONFIDENTIAL  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF HUBBELL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF HUBBELL IS PROHIBITED.

12000 Crownpoint Dr., Suite 165 San Antonio, TX 78233		AccelTex Solutions	
TITLE:		2.4/5/6 GHz 4/7/7 dBi 4 Element Indoor/Outdoor Patch Antenna w/ RPSMA	
SIZE: C		DWG. NO. ATS-03674	
SCALE: 1:3		WEIGHT:	
SHEET 1 OF 1		REV 1	

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
1			INITIAL RELEASE		
REVISIONS					

4

3

2

1