



REV	DATE	DESCRIPTION	ECO	BY	C'H.K.
A	11/01/19	REVISION UPDATED	52356	SS	WP

ITEM NUMBER	CATALOG NUMBER	MATERIAL	COLOR	DIMENSIONS						SCREW SIZE	PKG.QTY
				A IN [MM]	B IN [MM]	D IN [MM]	E IN [MM]	F IN [MM]			
50056445	CTB075SF1C	NYLON 66	NATURAL,NO ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	100	
50056446	CTB075SF1M	NYLON 66	NATURAL,NO ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	1000	
50056447	CTB075AAF1C	NYLON 66	NATURAL,ACRYLIC ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	100	
50056448	CTB075AAF1CO	NYLON 66	BLACK,ACRYLIC ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	100	
50056449	CTB075AAF1M	NYLON 66	NATURAL,ACRYLIC ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	1000	
50056450	CTB075RAF1C	NYLON 66	NATURAL,RUBBER ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	100	
50056451	CTB075RAF1CO	NYLON 66	BLACK,RUBBER ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	100	
50056452	CTB075RZF1M	NYLON 66	NATURAL,RUBBER ADHESIVE	0.74 [19]	0.74 [19]	0.20 [5]	0.18 [5]	0.20 [5]	#10 [M5]	1000	



NOTES:



- MATERIAL:
NATURAL: POLYAMIDE 6.6 NATURAL
BLACK:POLYAMIDE 6.6 NATURAL
- FLAMMABILITY OF RAW MATERIAL : UL 94 - V2
- HUMIDITY ABSORPTION: 2.7% - 2.8% (23° C - 50% R.H.)
- INSTALLATION TEMPERATURE: -10° C / +50° C
- WORKING TEMPERATURE: -30° C / +85° C
- MAX SUSTAINABLE TEMPERATURE FOR SHORT TIME: +85°C
- GOOD RESISTANCE TO BASES, OILS, GREASES, OIL DERIVATES, CHLORIDE SOLVENTS. LIMITED RESISTANCE TO ACIDS. NOT RESISTANT TO PHENOLS.
- CARBON BLACK ADDITION GIVES A BETTER UV RESISTANCE
- IT IS RECOMMENDED THAT RUBBER BASED ADHESIVE MOUNTS DWELL 2 HOURS AFTER INSTALLATION, PRIOR TO LOADING. RUBBER BASED ADHESIVE TAPE IS THE BEST CHOICE FOR MOST ADHESIVE MOUNT APPLICATIONS, INCLUDING POWDER COATED SURFACES.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

CABLE TIE MOUNT PAD-LH-MP-20-3/4			
ITEM NO: SEE TABLE			
CAT. NO:SEE TABLE			
DRAWN BY: P.WINSON 07/02/2019			
CHECKER: K.JAYAVIGNESH 08/19/2019			
DSN APRVL: K.CASTOGUAY 11/19/2019			
MFG APRVL: --			
QA APRVL: B.ELLIOTT 11/11/2019			
MKT APRVL: K.BOUTIN 11/09/2019			
PROD FAM: --	DRAWING NO	REV	
PROJECT #: --	SIZE	50101822	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 3	
REL LEVEL: Released			

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	11/01/19	REVISION UPDATED	52356	SS	WP

ITEM NUMBER	CATALOG NUMBER	MATERIAL	COLOR	DIMENSIONS						SCREW SIZE	PKG.QTY
				A IN [MM]	B IN [MM]	D IN [MM]	E IN [MM]	F IN [MM]	H IN [MM]		
50056459	CTB100SF2C	NYLON 66	NATURAL, NO ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	100
50056460	CTB100AAF2C	NYLON 66	NATURAL, ACRYLIC ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	100
50056462	CTB100AAF2D	NYLON 66	NATURAL, ACRYLIC ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	500
50056461	CTB100AAF2C0	NYLON 66	BLACK, ACRYLIC ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	100
50056466	CTB100RAF2C	NYLON 66	NATURAL, RUBBER ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	100
50056463	CTB100RAF2C	NYLON 66	NATURAL, RUBBER ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	100
50056467	CTB100RAF2L	NYLON 66	NAUTRAL, RUBBER ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	50
50056464	CTB100RAF2C0	NYLON 66	BLACK, RUBBER ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	100
50056465	CTB100RAF2D	NYLON 66	NATURAL, RUBBER ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	500
50056453	CTB150AAF3C	NYLON 66	NATURAL, ACRYLIC ADHESIVE	1.10 [28]	1.10 [28]	0.23 [6]	0.21 [5]	0.17 [4]	0.09 [2]	#10 [M5]	100



NOTES:

- MATERIAL:
NATURAL: POLYAMIDE 6.6 NATURAL.
BLACK:POLYAMIDE 6.6 NATURAL.
- FLAMMABILITY OF RAW MATERIAL : UL 94 - V2.
- HUMIDITY ABSORPTION: 2.7% - 2.8% (23° C - 50% R.H.).
- INSTALLATION TEMPERATURE: -10° C / +50° C.
- WORKING TEMPERATURE: -30° C / +85° C.
- MAX SUSTAINABLE TEMPERATURE FOR SHORT TIME: +85°C.
- GOOD RESISTANCE TO BASES, OILS, GREASES, OIL DERIVATES, CHLORIDE SOLVENTS. LIMITED RESISTANCE TO ACIDS. NOT RESISTANT TO PHENOLS.
- CARBON BLACK ADDITION GIVES A BETTER UV RESISTANCE.
- IT IS RECOMMENDED THAT RUBBER BASED ADHESIVE MOUNTS DWELL 2 HOURS AFTER INSTALLATION, PRIOR TO LOADING. RUBBER BASED ADHESIVE TAPE IS THE BEST CHOICE FOR MOST ADHESIVE MOUNT APPLICATIONS, INCLUDING POWDER COATED SURFACES.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.





TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

CABLE TIE MOUNT PAD -LH-MP-30-1	
ITEM NO: SEE TABLE	
CAT. NO:SEE TABLE	
DRAWN BY: P.WINSON	07/02/2019
CHECKER: K.JAYAVIGNESH	08/19/2019
DSN APRVL: K.CASTOGUAY	11/19/2019
MFG APRVL: --	
QA APRVL: B.ELLIOTT	11/11/2019
MKT APRVL: K.BOUTIN	11/09/2019
PROD FAM: --	
PROJECT #: --	SIZE
DOCUMENT TYPE: SALES	50101822
REL LEVEL: Released	B
DRAWING NO	REV
50101822	A
SHEET 2 OF 3	




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	11/01/19	REVISION UPDATED	52356	SS	WP

ITEM NUMBER	CATALOG NUMBER	MATERIAL	DIMENSIONS														
			SIZE IN [MM]	DESCRIPTION	A IN [MM]	B IN [MM]	C IN [MM]	D IN [MM]	E IN [MM]	F IN [MM]	G IN [MM]	H IN [MM]	J IN [MM]	K (REF) IN [MM]	M IN [MM]	SCREW SIZE	PKG.QTY
50056454	CTB150AAF3D	NYLON 66	1.57 x 1.57 [40x 40]	NATURAL, ACRYLIC ADHESIVE	0.21 [5]	0.08 [2]	1.50 [38]	0.37 [9]	0.10 [2]	0.16 [4]	0.11 [3]	0.37 [9]	1.08 [27]	0.24 [6]	0.04 [1]	#1/4 [M6]	500
50056456	CTB150RAF3C0	NYLON 66	1.57 x 1.57 [40x 40]	BLACK, RUBBER ADHESIVE	0.21 [5]	0.08 [2]	1.50 [38]	0.37 [9]	0.10 [2]	0.16 [4]	0.11 [3]	0.37 [9]	1.08 [27]	0.24 [6]	0.04 [1]	#1/4 [M6]	100
50056457	CTB150RAF3D	NYLON 66	1.57 x 1.57 [40x 40]	NATURAL, RUBBER ADHESIVE	0.21 [5]	0.08 [2]	1.50 [38]	0.37 [9]	0.10 [2]	0.16 [4]	0.11 [3]	0.37 [9]	1.08 [27]	0.24 [6]	0.04 [1]	#1/4 [M6]	500
50056458	CTB150SF3C	NYLON 66	1.57 x 1.57 [40x 40]	NATURAL, NO ADHESIVE	0.21 [5]	0.08 [2]	1.50 [38]	0.37 [9]	0.10 [2]	0.16 [4]	0.11 [3]	0.37 [9]	1.08 [27]	0.24 [6]	0.04 [1]	#1/4 [M6]	100
10023753	CTB150RA4C	NYLON 66	1.57 x 1.57 [40x 40]	NATURAL, RUBBER ADHESIVE	0.21 [5]	0.08 [2]	1.50 [38]	0.37 [9]	0.10 [2]	0.16 [4]	0.11 [3]	0.37 [9]	1.08 [27]	0.24 [6]	0.04 [1]	#1/4 [M6]	100



DETAIL A
SCALE 8 : 1



NOTES:

- MATERIAL:
NATURAL: POLYAMIDE 6.6 NATURAL.
BLACK: POLYAMIDE 6.6 NATURAL.
- FLAMMABILITY OF RAW MATERIAL : UL 94 - V2.
- HUMIDITY ABSORPTION: 2.7% - 2.8% (23° C - 50% R.H.).
- INSTALLATION TEMPERATURE: -10° C / +50° C.
- WORKING TEMPERATURE: -30° C / +85° C.
- MAX SUSTAINABLE TEMPERATURE FOR SHORT TIME: +85°C.
- GOOD RESISTANCE TO BASES, OILS, GREASES, OIL DERIVATES, CHLORIDE SOLVENTS. LIMITED RESISTANCE TO ACIDS. NOT RESISTANT TO PHENOLS.
- CARBON BLACK ADDITION GIVES A BETTER UV RESISTANCE.
- IT IS RECOMMENDED THAT RUBBER BASED ADHESIVE MOUNTS DWELL 2 HOURS AFTER INSTALLATION, PRIOR TO LOADING. RUBBER BASED ADHESIVE TAPE IS THE BEST CHOICE FOR MOST ADHESIVE MOUNT APPLICATIONS, INCLUDING POWDER COATED SURFACES.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		CABLE TIE MOUNT PAD LH-MP-40-1.5	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: P.WINSON 07/02/2019	
		CHECKER: K.JAYAVIGNESH 08/19/2019	
		DSN APRVL: K.CASTOQUAY 11/19/2019	
		MFG APRVL: --	
		QA APRVL: B.ELLIOTT 11/11/2019	
		MKT APRVL: K.BOUTIN 11/09/2019	
		PROD FAM: --	
		DRAWING NO	
		50101822	
		REV	
		A	
		SHEET 3 OF 3	