


Post	P250041S0430	1
Suspension	S025040S0000	1
Anchor Shackle	AS-50	2
Part Number		Qty



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C2911-1988

DRY 60 HZ FLASHOVER	390
WET 60 HZ FLASHOVER	355
IMPULSE POSITIVE FLASHOVER	600
IMPULSE NEGATIVE FLASHOVER	660

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	265
IMPULSE POSITIVE WITHSTAND	540
IMPULSE NEGATIVE WITHSTAND	590

MAX WORKING LOADS, LBS(KN)

VERTICAL	10050 (44.6)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	1715 (7.6)
LEAKAGE DISTANCE	104
STRIKE DISTANCE	398

REV DATE 03/31/08

**OHM/BASS**  
TOLERANCE CHART

**HUBBELL POWER SYSTEMS**

TITLE: QUADRI SIL BRACED LINE POST ASSY

DATE / PART / ASSY NO: BLP041F00000

REV: 0

DO NOT SCALE THIS DRAWING

DWN BY: JVR DATE: 03/31/08 SHEET 1 OF 1

COMPROMISE THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE HOLDER ASSUMES NO LIABILITY FOR DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.