


Post	P250043S00030	1
Suspension	S025060S00000	1
Anchor Shackle	AS-50	2
Part Number	Qty	



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C2911-1988

DRY 60 HZ FLASHOVER	435
WET 60 HZ FLASHOVER	395
IMPULSE POSITIVE FLASHOVER	670
IMPULSE NEGATIVE FLASHOVER	780

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	295
IMPULSE POSITIVE WITHSTAND	600
IMPULSE NEGATIVE WITHSTAND	700

MAX WORKING LOADS, LBS(KN)

VERTICAL	1130 (49.4)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	1625 (7.2)
LEAKAGE DISTANCE	113
STRIKE DISTANCE	44.3

REV DATE 03/31/08

OHM/BASS
TOLERANCE CHART

HUBBELL POWER SYSTEMS

QUADRI SIL BRACED LINE POST ASSY

CONFERENTIAL THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE HOLDER ASSUMES NO LIABILITY FOR REPRODUCTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

DO NOT SCALE THIS DRAWING

DATE 03/31/08

SHEET 1 OF 1