


BURNDY CAT. NO.	WIRE SIZE	D1 in [mm]	D2 in [mm]	L1 in [mm]	RECCOMENDED TOOLING		
					DIELESS TOOLING	35, 750, 46 	
						NEST	INDENTOR
YF2/022UIL	2/0 CLASS H,I,K,M,DLO	0.48 [12.1]	0.57 [14.6]	0.87 [22.0]	81K SERIES (1)	U26F1	UY27F1
YF3/025UIL	3/0 CLASS G,H,I,K,M,DLO	0.56 [14.2]	0.66 [16.7]	0.98 [25.0]		U27F1	
YF4/032UIL	4/0 CLASS G*,H,I,K,M,DLO	0.59 [15.0]	0.69 [17.5]	1.26 [32.0]		U28F1	UY31F1
YF25032UIL	250 kcmil CLASS G*,H,I,K, 262 DLO	0.68 [17.3]	0.78 [19.8]	1.26 [32.0]		U29F1	
YF35032UIL	350 kcmil CLASS G,H,I,K, 373 DLO	0.81 [20.5]	0.93 [23.5]	1.26 [32.0]		U31F1	

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	09/02/2024	CREATED NEW DRAWING	240828042135	RA	YR



NOTES:

1. MATERIAL: COPPER.
2. FINISH : TIN PLATED
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
4. UL LISTED BARE AND COVERED FERRULES PER UL 486L REQUIREMENTS.
- USE PUADP1 ADAPTOR WITH THE USE OF U-DIES IN 46 SERIES CRIMP TOOLS.
- 6 * UL LISTING LIMITED TO 81K SERIES TOOLING.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-387-6487 FOR PRODUCT INFO: http://www.burndy.com	UNINSULATED FERRULES				
	ITEM NO: NA				
	CAT. NO:SEE TABLE				
	DRAWN BY: R.VASANTH		9/2/2024		
	CHECKER: C.BUCKLEY		10/31/2024		
	DSN APRVL: C.BUCKLEY		10/31/2024		
	MFG APRVL: --				
	QA APRVL: T.SWAN		10/31/2024		
	MKT APRVL: J.FRECHETTE		10/31/2024		
	PROD FAM: --				
	PROJECT #: --		SIZE	DRAWING NO	REV
	DOCUMENT TYPE: SALES		B	50149598	A
REL LEVEL: Released		SHEET 1 OF 1			

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-387-6487

FOR PRODUCT INFO: <http://www.burndy.com>

