


Post	P250051S0030	1
Suspension	S025075S0000	1
Anchor Shackle	AS-50	2
Part Number		Qty



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C2911-1988

DRY 60 HZ FLASHOVER	510
WET 60 HZ FLASHOVER	455
IMPULSE POSITIVE FLASHOVER	790
IMPULSE NEGATIVE FLASHOVER	895

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	340
IMPULSE POSITIVE WITHSTAND	710
IMPULSE NEGATIVE WITHSTAND	805

MAX WORKING LOADS, LBS(KN)

VERTICAL	11390 (50.6)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	1415 (6.2)
LEAKAGE DISTANCE	132
STRIKE DISTANCE	51.6

REV DATE 03/31/08

OHIE/BRASS
TOLERANCE CHART

HUBBELL POWER SYSTEMS

COMPROMISE: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE HOLDER ASSUMES NO LIABILITY FOR REPRODUCTION OR DISTRIBUTION OF COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

QUADRI SIL BRACED LINE POST ASSY

DO NOT SCALE THIS DRAWING

DATE 03/31/08

SHEET 1 OF 1