



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C29.11-1988

DRY 60 Hz FLASHOVER	510
WET 60 Hz FLASHOVER	455
IMPULSE POSITIVE FLASHOVER	790
IMPULSE NEGATIVE FLASHOVER	895

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 Hz 1-MIN WITHSTAND	340
IMPULSE POSITIVE WITHSTAND	710
IMPULSE NEGATIVE WITHSTAND	805

MAX WORKING LOADS, LBS(KN)

VERTICAL	11390 (50.6)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	1415 (6.2)

LEAKAGE DISTANCE	132
STRIKE DISTANCE	51.6

Post	P250051S0020	1
Suspension	S025075S0000	1
Anchor Shackle	AS-50	2
Part Number	Qty	

REV DATE 02/12/14

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.



TITLE QUADRI SIL BRACED LINE POST ASSY

SIZE B	DWG NO. --	CAT / PART / ASSY NO. BLP051G12000	REV 1
DO NOT SCALE THIS DRAWING	DRN BY JVR	DATE 03/31/08	SHEET 1 OF 1