



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C2911-1988

DRY 60 HZ FLASHOVER	530
WET 60 HZ FLASHOVER	470
IMPULSE POSITIVE FLASHOVER	830
IMPULSE NEGATIVE FLASHOVER	890

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	350
IMPULSE POSITIVE WITHSTAND	745
IMPULSE NEGATIVE WITHSTAND	800

MAX WORKING LOADS, LBS(KN)

VERTICAL	10240 (455)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	1300 (5.7)
LEAKAGE DISTANCE	145
STRIKE DISTANCE	54.4

Post	P250055S0430	1
Suspension	S025058S0000	1
Anchor Shackle	AS-50	2
Part Number		Qty

REV DATE 03/31/08

**OHIO BRASS**  
TOLERANCE CHART

**HUBBELL POWER SYSTEMS**

COMPENSATE THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE INFORMATION IS TO BE USED ONLY FOR THE PURPOSES INTENDED AND NO REPRODUCTION OR DISTRIBUTION OF COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. UNPUBLISHED ALL RIGHTS RESERVED UNDER THE PATENT LAWS.

DO NOT SCALE THIS DRAWING

DATE 03/31/08

SHEET 1 OF 1

QUADRI SIL BRACED LINE POST ASSY

REV 0