



Part Number	Qty
Post	1
Suspension	1
Anchor Shackle	2



ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C29.11-1988

DRY 60 HZ FLASHOVER	580
WET 60 HZ FLASHOVER	510
IMPULSE POSITIVE FLASHOVER	875
IMPULSE NEGATIVE FLASHOVER	980


ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	380
IMPULSE POSITIVE WITHSTAND	785
IMPULSE NEGATIVE WITHSTAND	880

MAX WORKING LOADS, LBS(KN)

VERTICAL	11,240 (49.9)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	1250 (5.5)
LEAKAGE DISTANCE	151
STRIKE DISTANCE	57

REV DATE 03/02/09


**HUBBELL POWER SYSTEMS**  
 TITLE QUADRI SIL BRACED  
 LINE POST ASSY  
 CONVENTIONAL THE DRAWING AND ITS  
 CONTENTS ARE CONFIDENTIAL AND THE  
 INFORMATION IS NOT TO BE DISCLOSED  
 TO ANY OTHER PARTY WITHOUT THE  
 WRITTEN PERMISSION OF HUBBELL  
 POWER SYSTEMS. UNAUTHORIZED  
 ALL RIGHTS RESERVED UNDER THE  
 COPYRIGHT LAWS.

SIZE	DMG NO.	CAT / PART / ASSY NO.	REV
B		BLP058G12000	1

DO NOT SCALE THIS DRAWING

DWG BY JVR DATE 03/26/08 SHEET 1 OF 1