


NOTES:

1	CREEPAGE DISTANCE:	IN.: 55.4" / 1408 mm	OUT.: 53.9" / 1369 mm
2	ARC DISTANCE:	IN.: 25.1" / 637 mm	OUT.: 22.9" / 582 mm
3	NOMINAL VOLTAGE:	69kV	
4	NOMINAL CURRENT:	1200A	
5	VOLTAGE WITHSTAND, 60 sec.:	160kV	
6	BIL:	350kV	
7	ROUTINE TEST ACCORDING TO:	IEEE C57.19.01	
8	WEIGHT:	192 lb / 87.1 kg	
9	MAX. TORQUE APPLIED ON FLANGE BOLTS:	70 lbf · ft / 94.9 N · m	
10	TRANSIENT SHORT-CIRCUIT CURRENT WITHSTAND :	63kA, 6 CYCLES.	

REVISIONS

ZONE	REV.	DESCRIPTION	DRAWN BY	DATE	APPR.
	A	NEW DESIGN	A.SAVARD	2022-03-08	J.V.



This drawing is the proprietary property of Electro Composites (2008) ULC, not part of the public domain, and is issued with the express understanding and agreement that it is not to be reproduced or copied in whole or in part or issued for furnishing information to others, or used directly or indirectly, in any way detrimental to the interest of Electro Composites (2008) ULC and is to be returned upon request by Electro Composites (2008) ULC. All Rights Reserved.