


Post	P250072S0420	1
Suspension	S025075S000A	1
Anchor Shackle	AS-50	2
Part Number		Qty



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C2911-1988

DRY 60 HZ FLASHOVER	685
WET 60 HZ FLASHOVER	585
IMPULSE POSITIVE FLASHOVER	1060
IMPULSE NEGATIVE FLASHOVER	1100

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	440
IMPULSE POSITIVE WITHSTAND	950
IMPULSE NEGATIVE WITHSTAND	985

MAX WORKING LOADS, LBS(KN)

VERTICAL	10010 (44.4)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	1015 (4.5)
LEAKAGE DISTANCE	189
STRIKE DISTANCE	68.7

REV DATE 03/31/08

**OHIO BRASS**  
TOLERANCE CHART

**HUBBELL POWER SYSTEMS**

COMPETITIVE THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE INFORMATION IS TO BE KEPT STRICTLY PRIVATE. NO REPRODUCTION OR DISTRIBUTION OF COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAW.

DO NOT SCALE THIS DRAWING

DATE 03/31/08

SHEET 1 OF 1

**QUADRI SIL BRACED LINE POST ASSY**

REV 0

DATE 03/31/08

DRN BY JVR

DATE 03/31/08

SHEET 1 OF 1