


Post	P250075S00030	1
Suspension	S025107S0000A	1
Anchor Shackle	AS-50	2
Part Number		Qty



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C2911-1988

DRY 60 HZ FLASHOVER	745
WET 60 HZ FLASHOVER	640
IMPULSE POSITIVE FLASHOVER	1140
IMPULSE NEGATIVE FLASHOVER	1240

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 HZ 1-MIN WITHSTAND	480
IMPULSE POSITIVE WITHSTAND	1025
IMPULSE NEGATIVE WITHSTAND	1115

MAX WORKING LOADS, LBS(KN)

VERTICAL	1120 (498)
TRANSVERSE TENSION	750 (33.3)
COMPRESSION	750 (33.3)
LONGITUDINAL	985 (4.3)
LEAKAGE DISTANCE	196
STRIKE DISTANCE	74

REV DATE 03/31/08

OHIE/BRASS
TOLERANCE CHART

HUBBELL POWER SYSTEMS

QUADRI SIL BRACED LINE POST ASSY

REV 1

DATE 03/24/08

DRN BY JVR

DATE 03/24/08

SHEET 1 OF 1

DO NOT SCALE THIS DRAWING

SIZE DWG NO. CAT / PART / ASSY NO. REV

B --- BLP075F12000 1

COMPRIENTIAL THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE RIGHTS ARE RESERVED UNDER THE PATENT SYSTEMS UNPUBLISHED HUBBELL POWER SYSTEMS. ALL RIGHTS RESERVED UNDER THE PATENT SYSTEMS UNPUBLISHED HUBBELL POWER SYSTEMS.