



[ACCESS 3D PORTAL CLICK HERE](#)

[ACCESS 3D PDF CLICK HERE](#)

NOTES:

1. MATERIAL - CASTING - ELECTRICAL BRONZE
2. HARDWARE - SILICON BRONZE OR STAINLESS STEEL NUTS, BOLTS AND LOCKWASHERS "ED" SUFFIX DICTATES BRONZE HARDWARE.
3. FOR ANGLE TONGUE ADD TO CAT NO. EXAMPLE: SWHD-025-B2-90

210608008976	06/08/2021	HG	HG	PTB
EC #	DATE	CHG BY	CKD BY	APPD BY
DESC OF DWG: UPDATE 3D FILE				
REASON (S) FOR CHANGE: --				
DISPOSITION OF MATERIAL: --				

THIRD ANGLE PROJECTION

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

**HUBBELL POWER SYSTEMS, Inc.**

TITLE  
COPPER ALLOY TERMINAL CONNECTOR  
2 CABLES TO FLAT

CATALOG NUMBER: SWHD FAMILY (SEE TABLE)

SIZE	DWG NO.	PART / ASSY NO.	REV
C	C-1357	--	34

SCALE: NS    DRN BY: EL    DATE: 02/15/57    SHEET 1 OF 2

CATALOG NUMBER	CABLE RANGE	FIG NO	A	B	C	D	E	F	G	J	K	L
SWHD025B2	#4 - 250 MCM	2	2.500	3.500	2.000	3.250	0.313	0.750	1.1875	0.500	0.625	6.188
SWHD025B290	#4 - 250 MCM	2	2.813	3.500	2.000	3.250	0.313	--	1.1875	0.500	0.625	
SWHD025B2X/Y45	#4 - 250 MCM	2	2.813	3.500	2.000	3.250	0.313	--	1.1875	0.500	0.625	
SWHD025C	#4 - 250 MCM	1	2.500	3.500	3.000	3.250	0.313	0.625	1.1875	0.500	0.625	6.188
SWHD025CX/Y90	#4 - 250 MCM	1	2.813	3.500	3.000	3.250	0.313	--	1.1875	0.500	0.625	
SWHD050B2	1/0 SOL - 500 MCM	2	2.750	3.813	2.000	3.250	0.656	1.281	1.375	0.500	0.625	6.375
SWHD050B2X/Y90	1/0 SOL - 500 MCM	2	2.750	3.813	2.000	3.250	0.656	--	1.375	0.500	0.625	
SWHD050C	1/0 SOL - 500 MCM	1	2.750	3.813	3.000	3.250	0.500	1.125	1.375	0.500	0.625	6.875
SWHD050CX/Y45	1/0 SOL - 500 MCM	1	2.750	3.813	3.000	3.250	0.500	--	1.375	0.500	0.625	
SWHD050CX/Y90	1/0 SOL - 500 MCM	1	3.125	3.813	3.000	3.250	0.375	--	1.375	0.500	0.625	
SWHD050D	1/0 SOL - 500 MCM	1	2.750	3.813	4.000	4.250	0.500	1.125	1.375	0.500	1.125	7.438
SWHD050DX/Y90	1/0 SOL - 500 MCM	1	3.125	3.813	4.000	4.250	0.375	--	1.375	0.500	1.125	
SWHD080C	500 - 800 MCM	1	2.750	4.688	3.000	3.250	0.500	1.250	1.8125	0.500	0.625	6.500
SWHD080D	500 - 800 MCM	1	2.750	4.688	4.000	4.250	0.500	1.250	1.8125	0.500	1.125	7.250
SWHD080DX/Y45	500 - 800 MCM	1	2.750	4.688	4.000	4.250	0.375	--	1.8125	0.500	1.125	
SWHD080DX/Y90	500 - 800 MCM	1	3.125	4.688	4.000	4.250	0.375	--	1.8125	0.500	1.125	
SWHD100C	4/0 - 1000 MCM	1	2.750	4.813	3.000	3.250	0.500	1.125	1.875	0.500	0.625	6.625
SWHD100CX/Y90	4/0 - 1000 MCM	1	3.250	4.813	3.000	3.250	0.500	--	1.875	0.500	0.625	
SWHD100D	4/0 - 1000 MCM	1	2.750	4.813	4.000	4.250	0.500	1.125	1.875	0.500	1.125	7.250
SWHD100DX/Y45	4/0 - 1000 MCM	1	2.750	4.813	4.000	4.250	0.500	--	1.875	0.500	1.125	
SWHD100DX/Y90	4/0 - 1000 MCM	1	3.250	4.813	4.000	4.250	0.500	--	1.875	0.500	1.125	
SWHD100K	4/0 - 1000 MCM	1	2.750	4.813	5.000	5.250	0.375	1.188	1.875	0.500	1.250	8.750
SWHD150D	1000 - 1500 MCM	1	3.750	5.563	4.000	4.250	0.500	1.281	2.250	0.500	1.125	8.250
SWHD150DX/Y45	1000 - 1500 MCM	1	3.750	5.563	4.000	4.250	0.500	--	2.250	0.500	1.125	
SWHD150DX/Y90	1000 - 1500 MCM	1	4.313	5.563	4.000	4.250	0.500	--	2.250	0.500	1.125	
SWHD200D	500 - 2000 MCM	1	5.250	5.563	4.000	4.250	0.750	1.594	2.250	0.500	1.125	9.750
SWHD200DX/Y45	500 - 2000 MCM	1	5.250	5.563	4.000	4.250	0.750	--	2.250	0.500	1.125	
SWHD200DX/Y90	500 - 2000 MCM	1	6.000	5.563	4.000	4.250	0.750	--	2.250	0.500	1.125	

CATALOG NUMBER: SWHD FAMILY (SEE TABLE)			
SIZE	DWG NO.	PART / ASSY NO.	REV
C	C-1357	--	34
SCALE: NS	DRN BY: EL	DATE: 02/15/57	SHEET 2 OF 2