

NOTES:

- 1) MATERIAL: 356-F ALUMINUM ALLOY.
2) CONNECTIONS CAN BE SUPPLIED WITH BONDED COPPER LINER BY ADDING SUFFIX "C" TO CATALOG TYPE. EXAMPLE: WCF-39B
3) ANGLE CONNECTORS CAN BE SUPPLIED IN MULTIPLES OF 15° AS SHOWN TO OBTAIN CORRECT ANGLE TAKE-OFF, ADD ANGLE DESIRED AND LETTER DESIGNATING SURFACE DESIRED. EXAMPLE: WCF-39B-X45
4) HOLE SPACING OTHER THAN SHOWN MUST BE SPECIFIED BY CUSTOMER.
5) "F" TONGUE WILL HAVE (4) .56 DIA HOLES ON 2.50 CENTERS
6) CONNECTORS WITH UNDRILLED TONGUES HAVE SAME DIMENSIONS AS CONNECTORS WITH DRILLED TONGUES.




FIG - 1

FIG - 2




FIG - 3

CABLE RANGE		CATALOG No.	FIG No.	DIMENSIONS IN INCHES								
DECIMAL	MCM DR AWG			A	B	C	D	E	F	G	H	K
.368-.373	1/0	WCF-39B	1	.75	4.25	1.50	3.25	.25	.56	.39	.81	.63
.398-.418	2/0	WCF-45B	1	.75	4.25	1.50	3.25	.25	.56	.45	.81	.63
.447-.470	3/0	WCF-50B	1	1.0	4.50	1.50	3.25	.31	.69	.50	1.0	.63
.502-.528	4/0	WCF-56B	1	1.0	4.50	1.50	3.25	.31	.69	.56	1.0	.63
.563-.593	250-266.8	WCF-63B	1	1.0	4.50	1.50	3.25	.31	.69	.63	1.0	.63
.563-.593	250-266.8	WCF-63C	2	1.0	4.50	3.0	3.25	.31	.69	.63	1.0	.63
.609-.642	300	WCF-67B	1	1.25	4.75	1.50	3.25	.38	.88	.67	1.31	.63
.625-.670	300-336.4	WCF-67C	2	1.25	4.75	3.0	3.25	.38	.75	.69	1.31	.63
.666-.684	336.4-350	WCF-72B	1	1.25	4.75	1.50	3.25	.38	.88	.72	1.31	.63
.666-.684	336.4-350	WCF-72C	2	1.25	4.75	3.0	3.25	.38	.88	.72	1.31	.63
.721-.728	397.5-400	WCF-78B	1	1.25	4.75	1.50	3.25	.38	.88	.72	1.31	.63
.721-.728	397.5-400	WCF-78C	2	1.25	4.75	3.0	3.25	.38	.88	.72	1.31	.63
.772-.795	450-477	WCF-83B	1	1.25	4.75	1.50	3.25	.38	.88	.83	1.31	.63
.772-.795	450-477	WCF-83C	2	1.25	4.75	3.0	3.25	.38	.88	.83	1.31	.63
.806-.846	500	WCF-88B	1	1.25	4.75	1.50	3.25	.38	.88	.88	1.31	.63
.806-.846	500	WCF-88C	2	1.25	4.75	3.0	3.25	.38	.88	.88	1.31	.63
.855-.883	550-556.5	WCF-92B2	1	1.50	5.0	2.0	3.25	.50	1.12	.92	1.63	.63
.855-.883	550-556.5	WCF-92C	2	1.50	5.0	3.0	3.25	.50	1.12	.92	1.63	.63
.891-.930	600-650	WCF-97B2	1	1.50	5.0	2.0	3.25	.50	1.12	.96	1.63	.63
.891-.930	600-650	WCF-97C	2	1.50	5.0	3.0	3.25	.50	1.12	.96	1.63	.63
.953-.977	700-715.5	WCF-103B2	1	1.50	5.0	2.0	3.25	.50	1.12	1.03	1.63	.63
.953-.977	700-715.5	WCF-103C	2	1.50	5.0	3.0	3.25	.50	1.12	1.03	1.63	.63
.990-1028	750-795	WCF-106B2	1	1.50	5.0	2.0	3.25	.50	1.12	1.06	1.63	.63
.990-1028	750-795	WCF-106C	2	1.50	5.0	3.0	3.25	.50	1.12	1.06	1.63	.63
1.031-1081	800-874.5	WCF-113B2	1	1.75	5.25	2.0	3.25	.63	1.38	1.12	1.88	.63
1.031-1081	800-874.5	WCF-113C	2	1.75	5.25	3.0	3.25	.63	1.38	1.12	1.88	.63
1.093-1125	900-954	WCF-117B2	1	1.75	5.25	2.0	3.25	.63	1.38	1.17	1.88	.63
1.093-1125	900-954	WCF-117C	2	1.75	5.25	3.0	3.25	.63	1.38	1.17	1.88	.63
1.140-1172	1000-1033.5	WCF-123B2	1	1.75	5.25	2.0	3.25	.63	1.38	1.23	1.88	.63
1.140-1172	1000-1033.5	WCF-123C	2	1.75	5.25	3.0	3.25	.63	1.38	1.23	1.88	.63
1.209-1246	1100-1113	WCF-129B2	1	2.0	5.50	2.0	3.25	.75	1.69	1.30	2.25	.63
1.209-1246	1100-1113	WCF-129C	2	2.0	5.50	3.0	3.25	.75	1.69	1.30	2.25	.63
.398-.418	2/0	WCF-45A	3	.75	2.75	1.50	2.0	.25	.56	.45	.81	.75
1.263-1315	1200-1300	WCF-136B2	1	2.0	5.50	2.0	3.50	.75	1.69	1.36	2.25	.63
1.263-1315	1200-1300	WCF-136C	2	2.0	5.50	3.0	3.50	.75	1.69	1.36	2.25	.63
1.364-1412	1400-1500	WCF-147B2	1	2.0	5.50	2.0	3.50	.75	1.69	1.46	2.25	.63
1.364-1412	1400-1500	WCF-147C	2	2.0	5.50	3.0	3.50	.75	1.69	1.46	2.25	.63
1.454-1504	1590-1700	WCF-155C	2	2.50	6.0	3.0	3.25	.75	1.75	1.55	2.63	.63
1.526-1590	1750-1900	WCF-162C	2	2.50	6.0	3.0	3.25	.75	1.75	1.63	2.63	.63
1.630-1631	2000	WCF-172C	2	2.50	6.0	3.0	3.25	.75	1.75	1.72	2.63	.63
1.340	1351-5	WCF-143B2	1	2.0	5.50	2.0	3.25	.75	1.69	1.39	2.25	.63
.741	336.4-307	WCF-78C	2	1.25	4.75	3.0	3.50	.38	.88	.78	1.31	.63
1.340	1351.5	WCF-143C	2	2.0	5.50	3.0	3.25	.75	1.69	1.39	2.25	.63
2.400	---	WCF-240-D	2	2.75	7.25	4.0	4.25	1.0	2.50	2.46	3.50	1.12
.609-.642	300	WCF-67-B2	1	1.25	4.75	2.0	3.50	.38	.88	.67	1.31	.63
.666-.684	336.4-350	WCF-72-B2	1	1.25	4.75	2.0	3.50	.38	.88	.72	1.31	.63
.721-.728	397.5-400	WCF-78-B2	1	1.25	4.75	2.0	3.50	.38	.88	.78	1.31	.63
.772-.795	450-477	WCF-83-B2	1	1.25	4.75	2.0	3.50	.38	.88	.83	1.31	.63
.806-.846	500	WCF-88-B2	1	1.25	4.75	2.0	3.50	.38	.88	.88	1.31	.63
.447-.470	3/0	WCF-50-C	2	1.0	4.50	3.0	3.50	.56	.69	.50	1.0	.63
.502-.528	4/0	WCF-56-C	2	1.0	4.50	3.0	3.50	.56	.69	.56	1.0	.63
.563	4/0 ACSR	WCF-59-B2	1	1.0	4.50	2.0	3.50	.38	.75	.59	1.25	.63
.563	4/0 ACSR	WCF-59-C	2	1.0	4.50	3.0	3.50	.38	.75	.59	1.25	.63
1.454-1504	1590-1700	WCF-155-B2	1	2.50	6.0	2.0	3.50	.75	1.75	1.55	2.63	.63
1.526-1590	1750-1900	WCF-162-B2	1	2.50	6.0	2.0	3.50	.75	1.75	1.63	2.63	.63

CABLE RANGE		CATALOG No.	FIG No.	DIMENSIONS IN INCHES								
DECIMAL	MCM DR AWG			A	B	C	D	E	F	G	H	K
1.630-1631	2000	WCF-172-B2	1	2.50	6.0	2.0	3.50	.75	1.75	1.72	2.63	.63
1.454-1504	1590-1700	WCF-155-D	2	2.50	6.75	4.0	4.12	.63	1.63	1.55	2.63	1.12
.772-.795	450-477	WCF-83-D	2	1.25	5.75	4.0	4.50	.38	.88	.83	1.31	1.12
2.4	---	WCF-240-D	2	2.75	7.25	4.0	4.25	1.0	2.50	2.47	3.50	1.12
1.031-1081	800-874.5	WCF-113-B2-90	1	1.75	---	2.0	3.50	.63	---	1.12	1.88	.63
1.209-1246	1100-1113	WCF-129-D-Y90	2	2.0	---	4.0	4.25	.56	---	1.30	2.25	1.12
1.263-1315	1200-1300	WCF-136-D-Y90	2	2.0	---	4.0	4.25	.56	---	1.36	2.25	1.12
1.364-1412	1400-1500	WCF-147-D-Y90	2	2.0	---	4.0	4.25	.56	---	1.47	2.25	1.12
1.209-1246	1100-1113	WCF-129-D-X/Y-45	2	2.0	---	4.0	4.25	.56	---	1.30	2.25	1.12
1.263-1315	1200-1300	WCF-136-D-X/Y-45	2	2.50	---	4.0	4.25	.75	---	1.55	2.62	1.12
.447-.470	3/0	WCF-50-C-Y-90	2	1.0	---	3.0	3.25	.31	---	.50	1.0	.63
.502-.528	4/0	WCF-56-C-Y-90	2	1.0	---	3.0	3.25	.31	---	.56	1.0	.63
.563-.593	250-266.8	WCF-63-C-Y-90	2	1.0	---	3.0	3.25	.31	---	.63	1.0	.63
.772-.795	450-477	WCF-83-B-Y-90	1	1.25	---	1.50	3.25	.38	---	.83	1.31	.63
1.729-1762	2250-2335.4	WCF-181-D-X/Y-45	2	2.75	---	4.0	4.25	1.0	---	1.81	3.25	1.12
1.823-1824	2500-918.27	WCF-188-D-X/Y-45	2	2.75	---	4.0	4.25	1.0	---	1.88	3.25	1.12
1.912	2750-91	WCF-197-D-X/Y-45	2	2.75	---	4.0	4.25	1.0	---	1.97	3.25	1.12
1.996-2158	3000-3500	WCF-222-D-X/Y-45	2	2.75	---	4.0	4.25	1.0	---	2.22	3.25	1.12
.953-.977	7000-715.5	WCF-103-F	---	1.50	7.75	6.0	6.0	.50	1.12	1.03	1.63	1.75
.666-.684	336.4-350	WCF-72-B2-Y90	1	1.25	---	2.0	3.25	.38	---	.72	1.31	.63
.990-1028	750-795	WCF-106-C-Y90	2	1.50	---	3.0	3.25	.50	---	1.06	1.63	.63
1.209-1246	1100-1113	WCF-129-B2-Y90	1	2.0	---	2.0	3.25	.75	---	1.30	2.25	.63
.609-.642	300	WCF-67-B-X/Y-45	1	1.25	---	1.50	3.25	.38	---	.67	1.31	.63
.666-.684	336.4-350	WCF-72-B-X/Y-45	1	1.25	---	1.50	3.25	.38	---	.72	1.31	.63
.721-.728	397.5-400	WCF-78-B-X/Y-45	1	1.25	---	1.50	3.25	.38	---	.78	1.31	.63
.772-.795	450-477	WCF-83-B-X/Y-45	1	1.25	---	1.50	3.25	.38	---	.83	1.31	.63
.806-.846	500	WCF-88-B-X/Y-45	1	1.25	---	1.50	3.25	.38	---	.88	1.31	.63
.855-.883	500-556.5	WCF-92-C-X/Y-45	2	1.50	---	3.0	3.25	.50	---	.92	1.63	.63
.891-.930	600-650	WCF-97-C-X/Y-45	2	1.50	---	3.0	3.25	.50	---	.97	1.63	.63
.953-.977	700-715.5	WCF-103-C-X/Y-45	2	1.50	---	3.0	3.25	.50	---	1.03	1.63	.63
.990-1028	750-795	WCF-106-C-X/Y-45	2	1.50	---	3.0	3.25	.50	---	1.06	1.63	.63
.990-1028	750-795	WCF-106-B2-X/Y-45	1	1.50	4.0	2.0	3.25	.50	---	1.06	1.63	.63
1.823-1824	2500-918.27	WCF-188-C	2	2.75	6.75	3.0	3.25	1.0	2.38	1.88	3.25	.63
1.454-1504	1590-1700	WCF-155-D-X/Y-90	2	2.50	---	4.0	4.25	.75	---	1.55	2.63	1.12
1.729-1762	2250-2335.4	WCF-181-D-X/Y-90	2	2.75	---	4.0	4.25	1.0	---	1.81	3.25	1.12
1.823-1824	250-918.27	WCF-188-D-X/Y-90	2	2.75	---	4.0	4.25	1.0	---	1.88	3.25	1.12
.990-1028	750-795	WCF-106-D	2	1.50	6.0	4.0	4.25	.50	1.12	1.06	1.63	1.12
.990-1028	750-795	WCF-106-D-15	2	1.50	---	4.0	4.25	.50	---	1.06	1.63	1.12
1.630-1631	2000	WCF-172-D-15	2	2.50	---	4.0	4.25	.75	---	1.72	2.63	1.12
.609-.642	300	WCF-67-B-X/Y-45	1	1.25	---	1.50	3.50	.25	---	.67	1.31	.63
1.093-1125	900-954	WCF-117-C-X/Y-90	2	1.75	---	3.0	3.25	.63	---	1.17	1.88	.63
1.526-1590	1750-1900	WCF-162-D-Y-90	2	2.50	---	4.0	4.25	.75	---	1.63	2.63	1.12
.772-.795	450-477	WCF-83-C-Y-90	2	1.25	---	3.0	3.25	.31	---	.77	1.31	.63
.855-.883	550-556.5	WCF-92-C-Y90	2	1.50	---	3.0	3.25	.50	---	.92	1.63	.63
.990-1028	750-795	WCF-106-D-90	2	1.50	---	4.0	4.25	.50	---	1.06	1.63	1.12
.666-.684	336.4-350	WCF-72C-Y90	2	1.25	---	3.0	3.25	.38	---	.72	1.31	.63
1.454-1504	1590-1700	WCF-155-D-X/Y-45	2	2.50	---	4.0	4.25	.75	---	1.55	2.62	1.12
1.093-1125	900-954	WCF-117-B2-Y-90	1	1.75	---	2.0	3.50	.63	---	1.12	1.88	.63