



CATALOG NUMBER		CABLE RANGE	DIMENSIONS IN INCHES				
STAINLESS STEEL HWD	GALV. STEEL HWD	MIN. - MAX.	A	B	C	J	H
GC-140-00		#8 SOL. - #4 STR.	1.000	1.156	2.500	.375	
GC-140-01	GC-140-G1	#4SOL. - 2/0 STR.	1.625	1.750	2.125	.500	
GC-140-02	GC-140-G2	2/0 STR. - 250 MCM	1.625	1.750	2.125	.500	1.063
GC-140-03	GC-140-G3	300 - 500 MCM	2.000	2.000	2.125	.500	1.188
GC-140-04	GC-140-G4	500 - 800 MCM	2.000	2.500	2.750	.500	
GC-140-05	GC-140-G5	750 - 1000 MCM	2.000	2.125	2.250	.500	
GC-140-06	GC-140-G6	#4SOL. - 2/0 STR.	1.688	2.000	2.500	.625	
GC-140-07	GC-140-G7	2/0 STR. - 250 MCM	1.688	2.000	2.500	.625	
GC-140-08	GC-140-G8	300 - 500 MCM	2.125	2.250	2.500	.625	
GC-140-09	GC-140-G9	500 - 800 MCM	2.125	2.500	2.500	.625	
GC-140-10	GC-140-G10	750 - 1000 MCM	2.125	2.500	2.500	.625	

**NOTES:**

- MATERIAL: BODY - CAST BRONZE  
HARDWARE - STAINLESS STEEL
- THE BOLT LENGTHS SHOWN ARE FOR CONNECTING TO 1/4" FLAT BAR.
- IF LONGER BOLTS ARE REQUIRED, ADD BAR THICKNESS IN INCHES AFTER CAT. NO.  
EXAMPLE: GC-140-01-2 = BOLT LENGTH REQUIRED FOR 2" THICK PLATE.
- ITEMS WITH "WOS" SUFFIX HAVE WRENCH CLEARANCE AROUND BOLT HEAD.  
DIM'S A, B & C WILL REMAIN THE SAME.  
EX.: GC-140-01-WOS.
- TO OBTAIN ALUMINUM CONN. ADD PREFIX "A" TO CAT. NO.  
EX.: AGC-140-01- G/S HARDWARE WILL BE FURNISHED.

70168	06/19/2017	RK	HG
EC #	DATE	CHG BY	RESP ENG
DESC OF DWG:			
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:			

		<b>GROUND CLAMP TYPE - GC-140</b>	
SIZE <b>B</b>	DWG NO. <b>C-2705</b>	CAT / PART / ASSY NO.	
DO NOT SCALE THIS DRAWING		DRN BY RK	DATE 05/12/17
		SHEET 1 OF 1	REV 09

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS