


NOTES:

1. MATERIAL: CASTINGS - #255 ALLOY ELECTRICAL BRONZE
(EXCEPT MULTI CAPS - #112 ALLOY ALUMINUM BRZ.)
HARDWARE - SILICON BRONZE
2. ADD "TP" TO THE END OF CATALOG NUMBER TO ADD TIN PLATING.
FOR EXAMPLE: TTC8-04025TP.

65796	07/05/2016	RK	HG
EC #	DATE	CHG BY	RESP ENG
DESC OF DWG: REDRAWN IN AUTOCAD			
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:			

HPS

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS.
HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS

 HUBBELL® POWER SYSTEMS			
TITLE TEE CONNECTOR TUBE TO CABLE TYPE-TTC8			
SIZE B	DWG NO. C-4047	CAT / PART / ASSY NO. TTC8-(PER TAB)	REV 20
DO NOT SCALE THIS DRAWING	DRN BY PLW	DATE 12/14/54	SHEET 1 OF 3


CATALOG NUMBER	SIZE I.P.S.	CABLE RANGE		DIMENSION IN INCHES					
		MINIMUM	MAXIMUM	A	B	C	D	L	J
TTC8-04022-3	1/2	#6 SOL.	#2/0 STR.	2 1/2	5	2 1/2	2	3 7/8	3/8
TTC8-04025-3	1/2	#4 SOL.	250 MCM	2 1/2	5 1/8	2 1/2	1 7/8	4	3/8
TTC8-04025	1/2	#4 SOL.	250 MCM	2 1/2	5 3/8	2 1/2	2 3/8	4	1/2
TTC8-04050	1/2	1/0 SOL.	500 MCM	2 1/2	5 9/16	2 3/4	2 7/16	4 3/16	1/2
TTC8-06022-3	3/4	#6 SOL.	#2/0 STR.	2 1/2	5 1/4	2 1/2	2	4	3/8
TTC8-06025-3	3/4	#4 SOL.	250 MCM	2 1/2	5 3/8	2 3/4	1 7/8	4 1/8	3/8
TTC8-06025	3/4	#4 SOL.	250 MCM	2 1/2	5 9/16	2 1/2	2 5/16	4 1/4	1/2
TTC8-06050-3	3/4	1/0 SOL.	500 MCM	2 1/2	5 3/8	2 3/4	2 1/16	4 1/8	3/8
TTC8-06050	3/4	1/0 SOL.	500 MCM	3	6	2 3/4	2 7/16	4 1/2	1/2
TTC8-06100	3/4	4/0 STR.	1000 MCM	3	6 5/8	3 1/2	2 7/8	5 1/8	1/2
TTC8-10022	1	#6 SOL.	2/0 STR.	3 1/2	5 1/2	2 1/2	1 15/16	4	3/8 & 1/2
TTC8-10025-3	1	#4 SOL.	250 MCM	2 1/2	5 3/4	2 3/4	1 7/8	4 5/16	3/8
TTC8-10025	1	#4 SOL.	250 MCM	2 1/2	5 13/16	2 1/2	2 5/16	4 1/4	1/2
TTC8-10050-3	1	1/0 SOL.	500 MCM	3 3/4	5 7/8	2 3/4	2 1/8	4 1/2	3/8
TTC8-10050	1	1/0 SOL.	500 MCM	2 3/4	6 1/4	2 3/4	2 7/16	4 5/8	1/2
TTC8-10080-3	1	2/0 SOL.	800 MCM	3 3/4	5 7/8	2 3/4	2 3/8	4 1/2	3/8
TTC8-10080	1	2/0 SOL.	800 MCM	3 3/4	6 1/16	2 3/4	2 7/8	4 1/2	1/2
TTC8-10100	1	4/0 STR.	1000 MCM	3 3/4	6 13/16	3 1/2	2 7/8	5 1/4	1/2
TTC8-12025-3	1 1/4	#4 SOL.	250 MCM	2 1/4	5 7/8	2 1/2	1 7/8	4 3/8	3/8
TTC8-12025	1 1/4	#4 SOL.	250 MCM	2 1/4	6	2 1/2	2 5/16	4 5/16	1/2
TTC8-12050-3	1 1/4	1/0 SOL.	500 MCM	2 1/4	6	2 3/4	2 1/8	4 5/8	3/8
TTC8-12050	1 1/4	1/0 SOL.	500 MCM	3 3/4	6 7/16	2 3/4	2 7/16	4 3/4	1/2
TTC8-12080-3	1 1/4	2/0 SOL.	800 MCM	3 3/4	6 1/8	2 3/4	2 3/8	4 5/8	3/8
TTC8-12080	1 1/4	2/0 SOL.	800 MCM	3 3/4	6 7/16	2 3/4	2 7/8	4 5/8	1/2
TTC8-12100	1 1/4	4/0 STR.	1000 MCM	3 3/4	7 1/2	3 1/2	2 7/8	5 5/8	1/2
TTC8-12200	1 1/4	500 MCM	2000 MCM	2 3/4	7 11/16	4	3 5/16	5 15/16	1/2
TTC8-14025-3	1 1/2	#4 SOL.	250 MCM	2 3/4	6 1/8	2 1/2	2	4 5/8	3/8
TTC8-14025	1 1/2	#4 SOL.	250 MCM	2 3/4	6 7/16	2 1/2	2 5/16	4 9/16	1/2
TTC8-14050-3	1 1/2	1/0 SOL.	500 MCM	2 3/4	6 3/8	2 3/4	2 1/8	4 5/8	3/8
TTC8-14050	1 1/2	1/0 SOL.	500 MCM	2 3/4	6 9/16	2 3/4	2 7/16	4 3/4	1/2
TTC8-14080-3	1 1/2	2/0 SOL.	800 MCM	3 1/4	6 3/8	2 3/4	2 3/8	4 5/8	3/8
TTC8-14080	1 1/2	2/0 SOL.	800 MCM	3 1/4	6 11/16	2 3/4	2 7/8	4 13/16	1/2
TTC8-14100	1 1/2	4/0 STR.	1000 MCM	3 1/4	7 1/2	3 1/2	2 7/8	5 5/8	1/2
TTC8-14150	1 1/2	250 MCM	1500 MCM	4 1/4	7 3/4	3 3/4	3 1/8	5 7/8	1/2
TTC8-14200	1 1/2	500 MCM	2000 MCM	2 3/4	8	4 1/8	3 5/16	6 1/8	1/2

CATALOG NUMBER	SIZE I.P.S.	CABLE RANGE		DIMENSION IN INCHES					
		MINIMUM	MAXIMUM	A	B	C	D	L	J
TTC8-20025-3	2	#4 SOL.	250 MCM	2 1/4	6 5/8	2 1/2	2	4 3/4	3/8
TTC8-20025	2	#4 SOL.	250 MCM	2 1/2	7 1/8	2 1/2	2 5/16	4 7/8	1/2
TTC8-20050-3	2	1/0 SOL.	500 MCM	2 1/4	6 7/8	2 3/4	2 1/8	5	3/8
TTC8-20050	2	1/0 SOL.	500 MCM	2 1/4	7 3/8	2 3/4	2 7/16	5 1/8	1/2
TTC8-20080-3	2	2/0 SOL.	800 MCM	2 1/4	6 7/8	2 3/4	2 3/8	5	3/8
TTC8-20080	2	2/0 SOL.	800 MCM	2 3/4	7 3/8	2 3/4	2 7/8	5 1/8	1/2
TTC8-20100	2	4/0 STR.	1000 MCM	3 1/4	8 1/8	3 1/2	2 7/8	5 7/8	1/2
TTC8-20150	2	250 MCM	1500 MCM	3 1/4	8 3/8	3 3/4	3 5/16	6 1/8	1/2
TTC8-20200	2	500 MCM	2000 MCM	3 1/4	8 3/4	4	3 3/8	6 1/2	1/2
TTC8-24025-3	2 1/2	#4 SOL.	250 MCM	2 1/4	7 1/4	2 1/2	2	5	3/8
TTC8-24025	2 1/2	#4 SOL.	250 MCM	2 1/2	7 3/8	2 1/2	2 1/4	5	1/2
TTC8-24050-3	2 1/2	1/0 SOL.	500 MCM	2 1/4	7 1/2	2 3/4	2 1/8	5 1/4	3/8
TTC8-24050	2 1/2	1/0 SOL.	500 MCM	2 1/2	7 3/4	2 3/4	2 7/16	5 3/8	1/2
TTC8-24080-3	2 1/2	2/0 SOL.	800 MCM	2 1/4	7 1/2	2 3/4	2 3/8	5 1/4	3/8
TTC8-24080	2 1/2	2/0 SOL.	800 MCM	3 1/4	7 5/8	2 3/4	2 7/8	5 1/4	1/2
TTC8-24100	2 1/2	4/0 STR.	1000 MCM	2 1/4	8 3/8	3 1/2	2 7/8	6	1/2
TTC8-24150	2 1/2	250 MCM	1500 MCM	3 1/4	8 5/8	3 3/4	3 5/16	6 1/4	1/2
TTC8-24200	2 1/2	500 MCM	2000 MCM	3 1/4	8 7/8	4	3 5/16	6 1/2	1/2
TTC8-30025-3	3	#4 SOL.	250 MCM	2 1/4	7 3/4	2 1/2	2	5 1/4	3/8
TTC8-30025	3	#4 SOL.	250 MCM	2 1/4	7 7/8	2 1/2	2 5/16	5 1/4	1/2
TTC8-30050-3	3	1/0 SOL.	500 MCM	2 1/4	8	2 3/4	2 1/8	5 1/2	3/8
TTC8-30050	3	1/0 SOL.	500 MCM	2 1/2	8 1/4	2 3/4	2 7/16	5 5/8	1/2
TTC8-30080-3	3	2/0 SOL.	800 MCM	2 1/4	8	2 3/4	2 3/8	5 1/2	3/8
TTC8-30080	3	2/0 SOL.	800 MCM	3 1/2	8 5/16	2 1/8	2 3/4	5 5/8	1/2
TTC8-30100	3	4/0 STR.	1000 MCM	3 1/2	9 1/16	3 1/2	2 7/8	6 3/8	1/2
TTC8-30150	3	250 MCM	1500 MCM	3 1/2	9 5/16	3 3/4	3 5/16	6 5/8	1/2
TTC8-30200	3	500 MCM	2000 MCM	3 1/2	9 9/16	4	3 5/16	6 7/8	1/2
TTC8-34025-3	3 1/2	#4 SOL.	250 MCM	2 1/4	8 1/4	2 1/2	2	5 1/2	3/8
TTC8-34025	3 1/2	#4 SOL.	250 MCM	2 1/4	8 1/2	2 1/2	2 3/8	5 5/8	1/2
TTC8-34050-3	3 1/2	1/0 SOL.	500 MCM	2 1/4	8 1/2	2 3/4	2 1/8	5 3/4	3/8
TTC8-34050	3 1/2	1/0 SOL.	500 MCM	2 1/4	8 3/4	2 3/4	2 1/2	5 5/8	1/2
TTC8-34080-3	3 1/2	2/0 SOL.	800 MCM	2 1/4	8 1/2	2 3/4	2 3/8	5 3/4	3/8
TTC8-34080	3 1/2	2/0 SOL.	800 MCM	2 1/4	8 3/4	2 3/4	2 7/8	5 5/8	1/2
TTC8-34100	3 1/2	4/0 STR.	1000 MCM	2 1/4	9 1/2	3 1/2	2 7/8	6 5/8	1/2
TTC8-34150	3 1/2	250 MCM	1500 MCM	2 1/2	9 15/16	3 3/4	3 5/16	6 29/32	1/2
TTC8-34200	3 1/2	500 MCM	2000 MCM	2 1/4	10	4	3 3/8	7 1/8	1/2

65796	07/05/2016	RK	HG
EC #	DATE	CHG BY	RESP ENG
DESC OF DWG: REDRAWN IN AUTOCAD			
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:			

HPS

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS.
HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS

 **HUBBELL® POWER SYSTEMS**

TITLE: **TEE CONNECTOR TUBE TO CABLE TYPE-TTC8**

SIZE B	DWG NO. C-4047	CAT / PART / ASSY NO. TTC8-(PER TAB)	REV 20
DO NOT SCALE THIS DRAWING		DRN BY PLW	DATE 12/14/54
		SHEET	2 OF 3


4

3

2

1

CATALOG NUMBER	SIZE I.P.S.	CABLE RANGE		DIMENSION IN INCHES					
		MINIMUM	MAXIMUM	A	B	C	D	L	J
TTC8-40025-3	4	#4 SOL.	250 MCM	2 1/4	8 3/4	2 1/2	2	5 3/4	3/8
TTC8-40025	4	#4 SOL.	250 MCM	2 1/2	9 3/16	2 1/2	2 1/4	5 15/16	1/2
TTC8-40050-3	4	1/0 SOL.	500 MCM	2 1/4	9	2 3/4	2 1/8	6	3/8
TTC8-40050	4	1/0 SOL.	500 MCM	2 1/2	9 7/16	2 3/4	2 7/16	6 1/8	1/2
TTC8-40080-3	4	2/0 SOL.	800 MCM	2 1/4	9	2 3/4	2 3/8	6	3/8
TTC8-40080	4	2/0 SOL.	800 MCM	2 1/2	9 7/16	2 3/4	2 7/8	6 3/16	1/2
TTC8-40100	4	4/0 STR.	1000 MCM	2 1/2	10 3/16	3 1/2	2 7/8	6 7/8	1/2
TTC8-40150	4	250 MCM	1500 MCM	2 1/2	10 7/16	3 3/4	3 5/16	7 3/16	1/2
TTC8-40200	4	500 MCM	2000 MCM	4	10 11/16	4	3 5/16	7 3/8	1/2
TTC8-50025	5	#4 SOL.	250 MCM	5	10 3/4	2 7/16	2 1/4	6 5/8	5/8 & 1/2
TTC8-50050	5	1/0 SOL.	500 MCM	5	11 5/16	2 3/4	2 7/16	7 3/16	5/8 & 1/2

65796	07/05/2016	RK	HG	HPS	 HUBBELL® POWER SYSTEMS POWER SYSTEMS, INC.		
EC #	DATE	CHG BY	RESP ENG				
DESC OF DWG: REDRAWN IN AUTOCAD				CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS	TITLE TEE CONNECTOR TUBE TO CABLE TYPE-TTC8		
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:					SIZE B	DWG NO. C-4047	CAT / PART / ASSY NO. TTC8-(PER TAB)
				DO NOT SCALE THIS DRAWING	DRN BY PLW	DATE 12/14/54	SHEET 3 OF 3

4

3

2

1