


1	CREEPAGE DISTANCE:	55.7" / 1415mm
2	ARC DISTANCE:	21.5" / 546mm
3	NOMINAL VOLTAGE:	27.5kV
4	NOMINAL CURRENT:	3000A
5	WITHSTAND VOLTAGE AT 60 sec.:	70kV
6	B.I.L. :	150kV
7	ROUTINE TEST ACCORDING TO:	CSA C88.1-96
8	MAX. TORQUE APPLIED ON FLANGE BOLTS:	70 lbf · ft / 94.9 N · m
9	WEIGHT:	146 lb / 66.2 Kg



6	1	S-1001-2022		CAPACITANCE TAP ASSEMBLY	ALUMINUM
5	1	S-3692-2417-0		CAP	COPPER
4	1	S-8140-7737		ROD ASSEMBLY	COPPER
3	1	S-8140-7736		SHIELD ASSEMBLY	COPPER
2	1	S-5392-4945		FLANGE	ALUMINUM
1	1	S-8140-7735	-001	CASTING, CYCLOALIPHATIC RESIN	EC-APG-02
ITEM NO.	QTY	DRAWING NO.	PART NO.	DESCRIPTION	NOTE / MAT'L
PARTS LIST					

TITLE: SDC® BUSHING 27.5kV, 3000A MODEL: 150-030-T-790-00			
FORMAT A	CAGE CODE	DRAWING NO. S-8140-7735	REVISION NR
SCALE 1:8			GENERATED BY: SolidWorks 2012
		SHEET	1 of 1