



NOTES:

1. MATERIAL: CASTING – 255 ELECTRICAL BRONZE
HARDWARE – STAINLESS STEEL
2. TO OBTAIN A TIN PLATED CASTING ADD "TP" SUFFIX TO CATALOG NO. (EXAMPLE: HDSF-14-D-12-12-TP)
3. ALL DIMENSIONS ARE IN INCHES
4. TO OBTAIN SILICON BRONZE HARDWARE ADD "ED" SUFFIX TO CATALOG NO. (EXAMPLE: HDSF-14-1-D-12-12-ED)
5. AMPACITY RATING: STANDARD– 2000 A
HTJC–2300 A

| CATALOG NO. | FIG. NO | STUD DIA./THD | A | B | J | K | L | T | W |
|-------------------|---------|---------------|-------|------|------|------|------|------|------|
| HDSF-14-1-D-12-12 | 2 | 1½-12 | 1.188 | 4.13 | ½-13 | 1.13 | 7.13 | 0.50 | 4.00 |
| HDSF-14-1-3-38-12 | 2 | 1½-12 | 1.188 | 3.13 | ½-13 | 0.63 | 6.00 | 0.38 | 3.00 |
| HDSF-20-1-D-12-12 | 2 | 2-12 | 1.188 | 4.13 | ½-13 | 1.13 | 7.25 | 0.50 | 4.00 |
| HDSF-12-1-D-38-12 | 2 | 1¼-12 | 1.188 | 4.13 | ½-13 | 1.13 | 7.00 | 0.38 | 4.00 |
| HDSF-12-1-D-38-14 | 2 | 1¼-14 | 1.188 | 4.13 | ½-13 | 1.13 | 7.00 | 0.38 | 4.00 |
| HDSF-12-1-D-38-0 | 2 | 1¼-SMOOTH | 1.188 | 4.13 | ½-13 | 1.13 | 7.00 | 0.38 | 4.00 |
| HDSF-14-1-D-38-12 | 2 | 1½-12 | 1.188 | 4.13 | ½-13 | 1.13 | 7.00 | 0.38 | 4.00 |



| | | | | | |
|--|------------|--------|----------|--|---|
| 67551 | 11/17/2016 | HG | HG | ANDERSON TOLERANCE CHART |  HUBBELL® POWER SYSTEMS |
| EC # | DATE | CHG BY | RESP ENG | | |
| DESC OF DWG: REDRAWN IN AUTOCAD ADD NOTE 4 AND CORRECTED NOTE 1 -- -- REASON (S) FOR CHANGE: -- DISPOSITION OF MAT'L: -- | | | | CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. | SIZE: - DWG NO.: CC-12926 CAT / PART / ASSY NO.: SEE CHART REV: 06 |
| | | | | | DO NOT SCALE THIS DRAWING DRN BY HDY DATE 1-17-84 SHEET 1 OF 1 |