



4			3							2			1		
CATALOG NUMBER	SIZE INDICATOR TAPE COLOR	CONDUCTOR APPLICATION	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	DIM G	ULT. BODY STRENGTH LB. [KN]	APPROX. WT. EACH LBS. [KG]	STANDARD PACK	ITEM	DESCRIPTION	MATERIAL
SW7195LB	ORANGE	ACSR/AAAC #2 - #6 AWG AAC #1 STR. - #6 SOL. AWG DIA. RANGE: .184 - .332	.720 [18.29]	.920 [23.37]	2.500 [63.50]	6.000 [152.40]	11.900 [302.26]	1.100 [27.94]	3.100 [78.74]	1000 [4.45]	.172 [.08]	100	1	BODY	ALUMINUM
SW7195FL			.720 [18.29]	.920 [23.37]	5.100 [129.54]	10.200 [259.08]	16.100 [408.94]	1.100 [27.94]	5.100 [129.54]	1000 [4.45]	.184 [.08]	100	2	KEEPER	ALUMINUM
SW7187LB	BLUE	ACSR/AAAC 1/0 - #4 AWG AAC 2/0 STR. - #2 SOL. AWG DIA. RANGE: .248 - .414	1.000 [25.40]	1.300 [33.02]	2.500 [63.50]	5.800 [147.32]	12.300 [312.42]	1.400 [35.56]	3.200 [81.28]	1200 [5.34]	.272 [.12]	50	3	RIGID BAIL	STAINLESS STEEL
SW7187FL			1.000 [25.40]	1.300 [33.02]	5.100 [129.54]	10.500 [266.70]	17.000 [431.80]	1.400 [35.56]	5.100 [129.54]	1200 [5.34]	.272 [.12]	25	4	FLEX BAIL	COVERED STAINLESS WIRE BRAID
SW7197LB	RED	ACSR/AAAC 4/0 - 2/0 AWG AAC 4/0 - 2/0 AWG DIA. RANGE: .414 - .565	1.200 [30.48]	1.400 [35.56]	2.700 [68.58]	5.700 [144.78]	12.900 [327.66]	1.500 [38.10]	3.400 [86.36]	1600 [7.12]	.284 [.13]	50	5	SIZE INDICATOR LABEL	PLASTIC
SW7197FL			1.200 [30.48]	1.400 [35.56]	5.100 [129.54]	10.100 [256.54]	17.200 [436.88]	1.500 [38.10]	5.100 [129.54]	1600 [7.12]	.297 [.13]	25	6	WARNING LABEL	PLASTIC



- NOTES:
- ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [kN], TORQUE IN. LBS. [N.m], & WEIGHT LBS. [KG]
 - RATINGS:
 - NA
 - CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:
 - NA
 - SUFFIXES & VARIANT CONFIGURATION:

A SUFFIX IS ADDED TO THE CATALOG NUMBER TO DESIGNATE THE REQUIRED FITTINGS AS SHOWN IN THE TABULATION (EXAMPLE: SW7195LBI):

 - "LB" - LOCKING BAIL
 - "FL" - FLEX BAIL
 - "I" - "GOLDEN", ANTI-CORROSION COATING VERSION.
 - PARTS PERFORMANCE TESTED REFERENCING ANSI C119.4 PULLOUT.
 - 6 ALL SIZES GET ORANGE WARNING TAPE PER ANSI Z535.4.
 - 7 ALL SIZES GET INDICATOR COLOR CODE TAPE.

230510030213	05/10/23	KM	TR	SP
EC #	DATE	CHANGED BY	CHECKED BY	APPROVED BY
DESCRIPTION:				WEIGHT, LBS
REDRAWN IN INVENTOR				SEE TABLE
CLAMP RANGE UPDATED FOR SW7195LB TO MATCH CATALOG				
TABLE UPDATED WITH BODY STRENGTH, WEIGHT AND				
STANDARD PACK				
--				
ADDITIONAL COMMENTS: --				

THIRD ANGLE PROJECTION

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS

HUBBELL POWER SYSTEMS, Inc.

TITLE: SW7195, SW7187, SW7197 SERVICE WEDGE

CATALOG NUMBER: SEE TABLE

SIZE C	DWG NO. CC-20598	PART / ASSY NO. SEE TABLE	REV 05
--------	------------------	---------------------------	--------

SCALE: 1 : 2 DRN BY: BAF DATE: 08/01/12 SHEET 1 OF 1