





CATALOG NO.	DIM "A"	DIM "B"	DIM "C"	DIM "D" INSIDE CHANNEL	MAXIMUM RECOMMENDED CABLE DIAMETER	WEIGHT	STANDARD PACK (PAIR)
FOSDA17ADSS	18.8 [477.5]	17 [431.8]	25 [635.00]	0.95 [24.13]	0.94 [23.9]	8 [3.62]	1
FOSDA12ADSS	13.6 [345.4]	11.7 [297.2]	18 [457.20]	0.75 [19.05]	0.68 [17.3]	4.70 [2.13]	1

ITEM	DESCRIPTION	MATERIAL
1	FIBER OPTIC STORAGE UNIT	POLYPROPYLENE
2	ADSS DIRECT ATTACH BRACKET	ALUMINIUM/PLASTIC
3	HEX BOLT 1/4" X 3-1/2	GALVANIZED STEEL
4	HEX BOLT 1/4" X 2-1/2	GALVANIZED STEEL
5	FLANGE NUT	STAINLESS STEEL
6	ACETAL TIE	ACETAL
7	POLE BLOCK	POLYPROPYLENE
8	RUBBER GROMMET	RUBBER



NOTES:

- ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [kN], TORQUE IN. LBS. [N.m], & WEIGHT LBS. [KG].
- RATINGS:
 - UV RESISTANT
- CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:
 - NA
- SUFFIXS & VARIANT CONFIGURATION:
 - NA
- PLASTIC FIBER OPTIC STORAGE UNITS USED ON ADSS CABLES.

79080	07/02/19	HD	RG	HPS.	HUBBELL® POWER SYSTEMS <small>POWER SYSTEMS, INC.</small>							
EC #	DATE	CHG BY	RESP ENG									
DESC OF DWG: REDRAWN IN INVENTOR NEW CC-TEMPLATE				CONFIDENTIAL: THIS DRAWING AND ITS CONTACTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS	TITLE FOSDA, FIBER OPTIC STORAGE PLASTIC FOR ADSS CABLES							
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:					<table border="1"> <tr> <td>SIZE</td> <td>DWG NO.</td> <td>CAT / PART / ASSY NO.</td> <td>REV</td> </tr> <tr> <td>C</td> <td>CC-21801</td> <td>SEE CHART</td> <td>01</td> </tr> </table>	SIZE	DWG NO.	CAT / PART / ASSY NO.	REV	C	CC-21801	SEE CHART
SIZE	DWG NO.	CAT / PART / ASSY NO.	REV									
C	CC-21801	SEE CHART	01									
DO NOT SCALE THIS DRAWING		DRN BY	JW	DATE	03/14/14	SHEET	1 OF 1					