


CAT. NO.	APPLICATION RANGE (MIN-MAX) IN. [MM]	"L" LENGTH IN. [MM]	"Ø" DIAMETER IN. [MM]	WEIGHT/BOX LBS [KG]	PCS/BOX
SVD103	.252-.327 [6.4-8.3]	49 [1240]	0.470 [11.940]	38.58 [17.50]	60
SVD104	.327-.461 [8.3-11.7]	51 [1300]	0.480 [12.190]	40.79 [18.50]	60
SVD105	.461-.563 [11.7-14.3]	53 [1350]	0.490 [12.445]	40.79 [18.50]	50
SVD106	.563-.760 [14.3-19.3]	65 [1640]	0.615 [15.620]	44.09 [20.00]	30

ITEM	DESCRIPTION	MATERIAL
1	DAMPER, SPIRAL VIBRATION	PVC



NOTES:

- ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [kN], TORQUE IN. LBS. [N.m], & WEIGHT LBS. [KG].
- RATINGS:
  - NA
- CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:
  - IEEE 664-1993, PARAGRAPH 4.3 POWER METHOD
  - IEEE 1591.2, PARAGRAPH 5.5.4.1.1
- SUFFIXES & VARIANT CONFIGURATION:
  - NA
- CATALOG NO. AND CABLE RANGE SIZE ARE STAMPED ON PRODUCT.
- SVD IS APPROVED FOR USE ON ADSS AND OPGW FIBER OPTIC CABLE AS WELL AS BARE CONDUCTOR.

220316018124	3/16/2022	AMC	AMC
EC #	DATE	CHG BY	RESP ENG
DESC OF DWG: MODIFY PACK QTYS			
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:			

HPS.  
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS

<b>HUBBELL® POWER SYSTEMS</b>			
TITLE <b>SVD CUSTOMER DRAWING</b>			
SIZE <b>B</b>	DWG NO. <b>CC-23211</b>	CAT / PART / ASSY NO. <b>REFER TO TABLE</b>	REV <b>04</b>
DO NOT SCALE THIS DRAWING	DRN BY <b>JES</b>	DATE <b>09/17/15</b>	SHEET <b>1 OF 1</b>