





**PCORE**  
ELECTRIC


|                                       |                                  |                            |
|---------------------------------------|----------------------------------|----------------------------|
| <b>KV CLASS</b> 34.5 kV               | <b>BIL.</b> 200 kV               | <b>U<sub>y</sub></b> 22 kV |
| <b>CURRENT RATING</b>                 |                                  |                            |
| 3000 AMP BOTTOM CONNECTION            |                                  |                            |
| <b>MIN. CREEP</b> 30.50 [774.7]       | <b>MIN. STRIKE</b> 14.00 [355.6] |                            |
| <b>CREEP/L-G</b> 1.53 [38.9]          | <b>STD.</b> IEEE C57.19.00/01    |                            |
| PCB CONTENT OF OIL IS LESS THAN 1 ppm |                                  |                            |

|                     |                       |                    |
|---------------------|-----------------------|--------------------|
| <b>DWG.</b>         | <b>CATALOG NUMBER</b> | <b>GLAZE COLOR</b> |
| SD                  | B-88833-144           | BROWN              |
| SD                  | B-88833-144-70        | LT. GRAY           |
| <b>TITLE</b>        |                       |                    |
| POC BUSHING         |                       |                    |
| LONGER ABOVE FLANGE |                       |                    |

|                                                         |                         |
|---------------------------------------------------------|-------------------------|
| <b>DATE</b> 1-10-02                                     | <b>REV. DATE</b> 7-6-21 |
| <b>MAXIMUM ALTITUDE</b> 10000 ft [3000 m]               |                         |
| <b>NET WEIGHT</b> 135 lb [62 kg]                        |                         |
| <b>ANGLE OF INCLINATION FROM THE VERTICAL</b> 0° TO 60° |                         |



**MOUNTING FLANGE DETAIL**



**FLANGE ALIGNMENT DIAGRAM  
TOP VIEW**

DIMENSIONS IN INCHES [MILLIMETERS]

**REVISION** CREEP/L-G WAS CREEP/U<sub>y</sub>, CORRECTED ROUNDING

**SCALE** 1/6

NOTE TO PURCHASER:  
ALL SALES OF PCORE PRODUCTS ARE SUBJECT  
TO OUR STANDARD TERMS AND CONDITIONS  
AND THE LIMITED WARRANTIES THEREUNDER