


NOTES:

1. THIS EXTENSION IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.
2. FURNISHED W/(4) 1/2-13 UNC X 8 [203] LONG SS HEX HEAD BOLTS, (8) ø1/2 SS FLAT WASHERS, AND (4) 1/2-13 UNC SS HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
CHK	ENG	APR	129# 59kg		LC S
APR	APR	APR	SCALE	DRAWING DESCRIPTION <b>QUAZITE® 30 X 48 X 24 EXTENSION</b> INTEGRAL BOTTOM STANDARD VERSION	REV
			NTS		A
			SIZE		4/13
PROJECT NUMBER			B		DRAWING NUMBER
				SHEET 1 OF 1	EOB304824B