


NOTES:

1. THIS EXTENSION IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.
2. FURNISHED W/(4) 1/2-13 UNC X 8 [203] LONG SS HEX HEAD BOLTS, (8) ø1/2 SS FLAT WASHERS, AND (4) 1/2-13 UNC SS HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.					
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
CHK	ENG	APR	161# 73kg		LC S
APR	APR	APR	SCALE	DRAWING DESCRIPTION QUAZITE® 30 X 60 X 24 EXTENSION W/INTEGRAL BOTTOM STANDARD VERSION	REV
			NTS		A
			SIZE		4/13
PROJECT NUMBER					DRAWING NUMBER
					EOB306024B
SHEET 1 OF 1					