



CATALOG NO.	APPLICATION RANGE	STRAND SIZE & CONSTRUCTION	MAXIMUM RBS	DIM A	DIM B	DIM C	COLOR	WEIGHT	STANDARD PACK	ITEM	DESCRIPTION	MATERIAL
										1	AWDE FORMED WIRE	ALUMINIUM CLAD STEEL
AWDE4108	0.204 TO 0.230 [5.18 TO 5.84]	3#10, 4M	4532 [20.1]	21.00 [533.40]	15.8 [401]	0.938 [23.83]	GREEN	16.00 [7.30]	50			
AWDE4110	0.231 TO 0.259 [5.87 TO 6.58]	3#9, 6M	6000 [26.7]	22.00 [558.80]	18 [457]	1.000 [25.40]	YELLOW	20.00 [9.10]	50			
AWDE4113	0.260 TO 0.291 [6.60 TO 7.39]	3#8, 8M	8000 [35.6]	24.00 [609.60]	20.3 [516]	1.000 [25.40]	BLUE	20.00 [9.10]	50			
AWDE4116	0.292 TO 0.336 [7.42 TO 8.53]	3#7, 7#10 (5/16"), 10M	10000 [44.5]	26.00 [660.00]	22.8 [579]	1.000 [25.40]	BLACK	30.00 [13.60]	50			
AWDE4119	0.337 TO 0.360 [8.56 TO 9.14]	3#6, 7#9 (11/32"), 12.5M	12500 [55.6]	29.00 [736.60]	24.8 [630]	1.063 [27.00]	YELLOW	33.00 [14.80]	50			
AWDE4120	0.361 TO 0.384 [9.17 TO 9.75]	14M	14000 [62.3]	31.00 [787.40]	28.8 [655]	1.063 [27.00]	BLUE	53.00 [24.00]	50			
AWDE4122	0.385 TO 0.410 [9.78 TO 10.41]	3#5, 7#8 (3/8"), 16M	16000 [71.2]	32.00 [812.80]	28 [711]	1.063 [27.00]	ORANGE	55.00 [25.00]	50			
AWDE4124	0.411 TO 0.430 [10.44 TO 10.92]	18M	18000 [80.1]	34.00 [863.60]	30 [762]	1.063 [27.00]	BLACK	29.00 [13.20]	25			
AWDE4125	0.431 TO 0.474 [10.95 TO 12.04]	7#7 (7/16")	20000 [89.0]	36.00 [914.40]	32.2 [818]	1.125 [28.58]	GREEN	32.00 [14.50]	25			
AWDE4126	0.431 TO 0.474 [10.95 TO 12.04]	20M	20000 [89.0]	36.00 [914.40]	30.3 [770]	1.125 [28.58]	YELLOW	22.00 [10.00]	10			
AWDE4128	0.475 TO 0.515 [12.07 TO 13.08]	7#6 (1/2")	22730 [101.1]	40.00 [1016.00]	31.5 [800]	1.188 [30.18]	BLUE	23.00 [10.50]	10			
AWDE4130	0.516 TO 0.535 [13.11 TO 13.59]	25M	25000 [111.2]	43.00 [1092.20]	36.7 [932]	1.188 [30.18]	RED	31.00 [14.10]	10			
AWDE4131	0.536 TO 0.570 [13.61 TO 14.48]	7#5	27030 [120.2]	45.00 [1143.00]	38.4 [975]	1.188 [30.18]	YELLOW	32.00 [14.50]	10			



- NOTES:
- ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [kN], TORQUE IN. LBS. [N.m], & WEIGHT LBS. [KG].
 - RATINGS:
 - ALL GUY WIRE DEAD-ENDS MEET 100% OF THE WIRE RATED BREAKING STRENGTH(RBS) AS SHOWN IN TABLE
 - CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:
 - NA
 - SUFFIXS & VARIANT CONFIGURATION
 - NA
 - HAND LAY DIRECTION: LEFT

79075	07/02/19	HD	RG	HPS.	HUBBELL® POWER SYSTEMS <small>POWER SYSTEMS, INC.</small>			
EC #	DATE	CHG BY	RESP ENG					
DESC OF DWG: MODIFIED RBS VALUES IN THE TABLE				CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS	TITLE AWDE, FORMED WIRE DEADENDS			
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:					<table border="1"> <tr> <td>SIZE C</td> <td>DWG NO. CC-18004</td> <td>CAT / PART / ASSY NO. SEE CHART</td> <td>REV 09</td> </tr> </table>	SIZE C	DWG NO. CC-18004	CAT / PART / ASSY NO. SEE CHART
SIZE C	DWG NO. CC-18004	CAT / PART / ASSY NO. SEE CHART	REV 09					
DO NOT SCALE THIS DRAWING		DRN BY BAF	DATE 05/10/06	SHEET 1 OF 1				