




			TITLE		DWG.	CATALOG NUMBER	UPPER PORCELAIN GLAZE COLOR
			PRC BUSHING		SD	B-89113-155	CHOCOLATE
DWG. DATE 11-29-00 REV. DATE			7.25 (184) B.C. 2.38 (60) LONGER BELOW FLANGE		SD	B-89113-155-70	LT. GRAY No. 70
MIN. CREEP	17.00 (432)	kV CLASS	15 kV	TEST STANDARD	CURRENT RATING		
CREEPAGE PER Uy	1.70 (43)	Uy	10 kV	NET WEIGHT	1200 AMP BOTTOM CONN.		
MIN. STRIKE DIST.	9.50 (241)	BIL	110 kV	ANGLE INCLINATION FROM VERTICAL = 0° TO 70°	@ 95°C MAX. OIL TEMPERATURE		



FLANGE ALIGNMENT DIAGRAM

NOTE TO PURCHASER
ALL SALES OF LAPP PRODUCTS ARE
SUBJECT TO OUR STANDARD TERMS
AND CONDITIONS AND THE LIMITED
WARRANTIES THEREUNDER

7A2A

LAST REVISION

DIMENSIONS IN INCHES (MILLIMETERS)