



MOUNTING BASE DETAIL

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C29.11-1988

DRY 60 Hz FLASHOVER	750
WET 60 Hz FLASHOVER	670
IMPULSE POSITIVE FLASHOVER	1160
IMPULSE NEGATIVE FLASHOVER	1255

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-60383

WET 60 Hz 1-MIN WITHSTAND	500
IMPULSE POSITIVE WITHSTAND	1040
IMPULSE NEGATIVE WITHSTAND	1125

MAX WORKING LOADS, LBS(KN)

VERTICAL	9960 (44.2)
TRANSVERSE TENSION	7500 (33.3)
COMPRESSION	7500 (33.3)
LONGITUDINAL	930 (4.1)

LEAKAGE DISTANCE	208
STRIKE DISTANCE	75.1

Post	P250080S0430	1
Suspension	S025084S000A	1
Anchor Shackle	AS-50	2
Part Number	Qty	

REV DATE 08/03/12

OHIO/BRASS
TOLERANCE CHART



HUBBELL POWER SYSTEMS

TITLE
QUADRI SIL BRACED
LINE POST ASSY

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

SIZE B	DWG NO. --	CAT / PART / ASSY NO. BLP080F00000	REV 1
DO NOT SCALE THIS DRAWING		DRN BY JVR	DATE 03/31/08
			SHEET 1 OF 1