



FIGURE 1

FIGURE 2

NOTES:

1. MATERIAL - BODY: BRONZE ALLOY
HARDWARE: SILICON BRONZE OR S.S.
(SEE BOM FOR DETAILS)
2. ADD SUFFIX "Tp" FOR TIN PLATED CASTINGS.
3. MAIN & TAP GROOVES ARE IDENTICAL. EACH WILL ACCEPT CU., CW, & CW/GS WIRE SIZES WITHIN THE FOLLOWING DECIMAL RANGES:

ST-3 = .125" TO .438" DIA. WIRES.
ST-4 = .162" TO .562" DIA. WIRES.

CATALOG NUMBER	FIGURE NUMBER	CONDUCTORS	CABLE RANGE		DIMENSIONS IN INCHES (MILLIMETERS)			
			MIN.	MAX.	A	B	C	J THD.
ST-3	2	COPPER COPPERWELD C/W GUY STRAND	#8 SOL.-2/0 STR. #8A - 2/0 F 1/8" - 7/16"	#8 SOL.-2/0 STR. #8A - 2/0 F 1/8" - 7/16"	7/8 (22.2)	1-1/2 (38.1)	1-1/2 (38.1)	5/16"-18
ST-4	1	COPPER COPPERWELD C/W GUY STRAND	#6 SOL.-4/0 STR. #6A - 4/0 F 1/4" - 9/16"	#6 SOL.-4/0 STR. #6A - 4/0 F 1/4" - 9/16"	15/16 (23.8)	1-7/8 (47.6)	1-1/2 (38.1)	3/8"-16

ANDERSON



HUBBELL® POWER SYSTEMS
PARALLEL GROOVE
CABLE CLAMP

37374	09/13/10	JA	JA
EC #	DATE	CHG BY	RESP ENG

DESC OF DWG:
-ADDED FIGURE 2.
-UPDATED THE CHART
--
--
REASON (S) FOR CHANGE: --
DISPOSITION OF MAT'L: --

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.			
TITLE	SIZE	DWG NO.	CAT / PART / ASSY NO.
PARALLEL GROOVE CABLE CLAMP	A	C-11339	SEE CHART
DO NOT SCALE THIS DRAWING	DRN BY	BAF	DATE 04/23/09
	SHEET	1	OF 1
	REV		08