



CATALOG NUMBER	CONDUCTOR SIZE		DIMENSIONS IN INCHES					
	MAIN MIN. - MAX.	TAP MIN. - MAX.	A	B	C	D	L	J
TCC4-022022	6 SOL. - 2/0 STR.	6 SOL. - #2/0 STR.	1.500	3.625	1.500	2.000	2.625	0.375
TCC4-025022	4 SOL. - 250 MCM	6 SOL. - 2/0 STR.	1.500	3.625	1.500	2.000	2.625	0.375
TCC4-025025	4 SOL. - 250 MCM	4 SOL. - 250 MCM	1.750	3.750	1.750	1.938	2.750	0.375
TCC4-025050	4 SOL. - 250 MCM	1/0 SOL. - 500 MCM	1.750	4.313	2.250	2.125	3.313	0.375
TCC4-050022	1/0 SOL. - 500 MCM	6 SOL. - 2/0 STR.	2.250	3.688	1.500	2.000	2.625	0.375
TCC4-050025	1/0 SOL. - 500 MCM	4 SOL. - 250 MCM	2.250	3.938	1.500	1.938	2.875	0.375
TCC4-050050	1/0 SOL. - 500 MCM	1/0 SOL. - 500 MCM	2.250	4.625	2.250	2.125	3.625	0.375
TCC4-080022	2/0 SOL. - 800 MCM	6 SOL. - #2/0 STR.	2.250	4.375	1.500	2.000	3.000	0.375
TCC4-080025	2/0 SOL. - 800 MCM	4 SOL. - 250 MCM	2.250	4.375	1.500	2.000	3.000	0.375
TCC4-080050	2/0 SOL. - 800 MCM	1/0 SOL. - 500 MCM	2.250	5.125	2.250	2.125	3.875	0.375
TCC4-100025	750 - 1000 MCM	#4 SOL. - 250 MCM	2.250	4.375	1.500	2.000	3.000	0.375
TCC4-100050	4/0 STR. - 1000 MCM	1/0 SOL. - 500 MCM	2.250	5.125	2.250	2.125	3.875	0.375
TCC4-150025	1000 - 1500 MCM	#4 SOL. - 250 MCM	2.250	4.625	1.500	2.000	3.250	0.375
TCC4-150050	1000 - 1500 MCM	250 - 500 MCM	2.250	5.375	2.250	2.125	4.000	0.375

NOTE: CLAMPS FOR 250 MCM AND SMALLER ARE FURNISHED WITH STANDARD MULTI-CAPS AS SHOWN ABOVE.

CASTING TOLERANCE CHART		
LESS THAN 2"	2"-6"	GREATER THAN 6"
±.031	±.047	±.063
ANGULAR TOLERANCE ± 1°		

NOTES:

- MATERIAL: CASTINGS - 255 ELEC. BRZ. ALLOY
HARDWARE - STAINLESS STEEL
- TO OBTAIN EVERDUR(SILICON BRONZE) HARDWARE ADD SUFFIX "ED" TO CATALOG. EX) TCC4-050025-ED
- TO TIN PLATE CASTINGS ADD SUFFIX "TP" TO CATALOG. EX)TCC4-050025-TP

71357	09/27/2017	AS	HG
EC #	DATE	CHG BY	RESP ENG
DESC OF DWG: PRODUCTION DRAWING CREATION			
REASON (S) FOR CHANGE: ADDED NOTE 2 AND 3 AND CHANGED HRDW DISPOSITION OF MAT'L:			

		TEE CONNECTOR CABLE TO CABLE TYPE-TCC4	
SIZE C	DWG NO. C-4053	CAT / PART / ASSY NO. TCC4 - (SEE TABLE)	REV 07
DO NOT SCALE THIS DRAWING	DRN BY TA	DATE 12 / 20 / 54	SHEET 1 OF 1