



CATALOG NUMBER	CODE NUMBER	FIG NUMBER	CONDUCTOR SIZE					DIE REF	DIMENSIONS - INCHES				
			7	19	37	61	91		127	A	B	C	E
BCL-016-B	6-20630	1	#4	*2				.640	6.00	2.00	1.19	0.25	
BCL-018-B	6-20630	1	*2	*2				.640	6.00	2.00	1.19	0.25	
BCL-019-B	6-20631	1	#1	#1				.640	6.75	3.00	1.50	0.38	
BCL-021-B	6-20631	1	1/0	1/0				.840	7.13	2.75	1.50	0.28	
BCL-022-B	6-20632	1	2/0	2/0				.840	7.13	2.75	1.50	0.28	
BCL-022-C	6-20632	1	2/0	2/0				.840	7.13	2.75	1.50	0.28	
BCL-023-B	6-20633	1	3/0	3/0				.840	7.13	2.75	1.50	0.28	
BCL-024-B	6-20634	1	4/0	4/0				.840	7.13	2.75	1.50	0.28	
BCL-024-C	6-20649	2	4/0	4/0				.840	7.88	2.75	3.00	0.29	
BCL-024-C-45	6-20649	2	4/0	4/0				.840	-	2.75	3.00	0.29	
BCL-024-C-X/Y-90	6-20635	2	4/0	4/0				.840	-	2.75	3.00	0.29	
BCL-025-B	6-20635	1		250	250			.840	7.13	2.75	1.50	0.28	
BCL-025-C	6-20636	2		250	250			.840	7.88	2.75	3.00	0.29	
BCL-030-B	6-20637	1		300	300			1.000	7.38	3.00	1.50	0.34	
BCL-030-B-X/Y-90	6-20638	1		300	300			1.000	-	3.00	1.50	0.34	
BCL-030-C	6-20638	2		300	300			1.000	8.06	3.00	3.00	0.29	
BCL-030-C-X/Y-90	6-20639	1		300	300			1.000	-	3.00	3.00	0.29	
BCL-035-B	6-20640	1		350	350			1.000	7.38	3.00	1.50	0.34	
BCL-035-B-X/Y-90	6-20640	1		350	350			1.000	-	3.00	1.50	0.34	
BCL-035-C	6-20640	2		350	350			1.000	8.06	3.00	3.00	0.29	
BCL-035-C-X/Y-90	6-20640	2		350	350			1.000	-	3.00	3.00	0.29	
BCL-040-C	6-20641	2		400	400			1.125	8.75	3.50	3.00	0.28	
BCL-050-B2	6-20641	1		500	500			1.125	7.88	3.50	1.75	0.38	
BCL-050-C	6-20642	2		500	500			1.125	8.75	3.50	3.00	0.28	
BCL-050-D	6-20642	2		500	500			1.125	9.31	3.50	4.00	0.48	
BCL-060-B2	6-20643	1		600	600			1.125	8.63	4.00	1.75	0.50	
BCL-075-B	6-20643	1		750	750			1.312	8.63	4.00	1.50	0.50	
BCL-075-B2	6-20643	1		750	750			1.312	8.63	4.00	1.50	0.50	
BCL-075-B2-X/Y-30	6-20644	1		750	750			1.312	-	4.00	1.75	0.50	
BCL-075-C	6-20644	2		750	750			1.312	9.00	4.00	3.00	0.28	
BCL-075-D	6-20644	2		750	750			1.312	9.75	4.00	4.00	0.42	
BCL-075-D-X/Y-90	6-20644	2		750	750			1.312	9.75	4.00	4.00	0.42	
BCL-080-B2	6-20645	1		800	800			1.500	8.88	4.00	2.00	0.63	
BCL-080-B2-X/Y-30	6-20645	1		800	800			1.500	-	4.00	2.00	0.63	
BCL-080-B2-X/Y-90	6-20645	1		800	800			1.500	8.88	4.00	2.00	0.63	
BCL-100-B2	6-20645	1		1000	1000			1.500	9.00	4.00	2.00	0.63	
BCL-100-B2-X/Y-30	6-20646	1		1000	1000			1.500	-	4.00	2.00	0.63	
BCL-100-C	6-20646	2		1000	1000			1.500	9.00	4.00	3.00	0.38	
BCL-100-D	6-20646	2		1000	1000			1.500	9.75	4.00	4.00	0.42	
BCL-100-D-AEP	6-20647	*2		1000	1000			1.500	9.75	4.00	4.00	0.42	
BCL-150-C	6-20651	2		1500	1500			2.125	10.18	5.00	3.00	0.75	
BCL-150-D	6-20651	2		1500	1500			2.125	11.25	5.00	4.00	0.75	
BCL-175-D	6-20651	2		1750	1750			2.375	12.25	6.00	4.00	0.75	
BCL-200-C	6-20648	2		2000	2000			2.375	11.18	6.00	3.00	1.00	
BCL-200-D	6-20648	2		2000	2000			2.375	12.38	6.00	4.00	0.70	

NOTES:
 1) MATERIAL - COPPER ALLOY CDA 11000
 2) FOR CRIMPING TOOLS AND DIES, REFER TO DIE REF AND MATCHING DIE REF. DN CC-4872 DR CC-5576
 *3) 'AEP' SUFFIX REQUIRES (4) .69 DIA HOLES DN 2.0 CENTERS IN TONGUE.

54259	2/3/14	JLB	JLB
EC #	DATE	CHG BY	RESP ENG

ANDERSON
TOLERANCE CHART

HUBBELL POWER SYSTEMS
 CU COMP. TERMINAL
 BCL-SEE CHART

DESC OF DWG	UPDATE BCL DIMENSIONS	SIZE	DWG NO.	CAT / PART / ASSY NO.	REV					
--	--	D	C-4402	BCL-XXX	35					
REASON (S) FOR CHANGE	DISPOSITION OF MAT'L	DO NOT SCALE THIS DRAWING	DRN BY	JLH	DATE	1/16/01	SHEET	1	OF	1