

4

3

2

1

CATALOG NUMBER	CONDUCTOR RANGE MAIN (MIN. - MAX.)	CONDUCTOR RANGE TAP (MIN. - MAX.)	CU MAIN (MIN. - MAX.)	CU TAP (MIN. - MAX.)	DIM A	DIM B	DIM C	DIM D	EYEBOLT HARDWARE	APPROX. WT. EACH LB. [KG]	STANDARD PACK	WRENCH/TOOL SIZE
S1530CC	.162 - .745 [4.12 - 18.96]	.162 - .528 [4.12 - 13.41]	#6 Sol - 400 MCM	#6 Sol - 4/0 Str.	1.375 [34.92]	6.750 [171.45]	1.690 [42.92]	60°	7/16"	1.590 [0.72]	25	11/16
S1534CC	.162 - .745 [4.12 - 18.96]	.162 - .528 [4.12 - 13.41]	#6 Sol - 400 MCM	#6 Sol - 4/0 Str.	1.375 [34.92]	6.750 [171.45]	1.690 [42.92]	60°	7/16"	1.590 [0.72]	25	3/4
S1540CC	.528 - 1.031 [13.41 - 26.24]	.198 - .703 [5.04 - 17.98]	4/0 Str. - 800 MCM	#4 Sol - 350 MCM	1.875 [48.00]	8.250 [210.00]	1.690 [42.92]	60°	1/2"	2.030 [0.92]	25	3/4
S1545CC	.953 - 1.466 [24.21 - 37.24]	.198 - .681 [5.03 - 17.30]	700 MCM - 1500 MCM	#4 Sol - 350 MCM	2.190 [56.00]	9.630 [245.00]	1.681 [42.705]	60°	1/2"	1.350 [0.61]	20	3/4

ITEM	DESCRIPTION	MATERIAL
1	BODY	BRONZE
2	GRIPPER	BRONZE
3	LOCKWASHER	STAINLESS STEEL
4	EYESTEM	BRONZE/ STAINLESS STEEL
5	PIN	STAINLESS STEEL
6	EYEBOLT	BRONZE
7	LOCK WASHER	STAINLESS STEEL
8	NUT	STAINLESS STEEL

NOTES:

1. ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [kN], TORQUE IN. LBS. [N.m], & WEIGHT LBS. [KG].

2. RATINGS:

A. RECOMMENDED TORQUE: EYEBOLT : 7/16" - 340 IN-LBS, 38 N.m
1/2" - 480 IN-LBS, 54 N.m
EYESTEM : 200 IN-LBS, 23 N.m

3. CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:

A. ANSI 119.4

4. A SUFFIX IS ADDED TO THE CATALOG NUMBER TO DESIGNATE THE REQUIRED FITTINGS AS SHOWN IN THE TABULATION (EXAMPLE: S1530GP):

"GP" - REPLACE SUFFIX "CC" WITH "GP" FOR TIN PLATED

"CGP" - REPLACE SUFFIX "CC" WITH "CGP" FOR TIN PLATED (EFFECTIVE 10/01/2021)

A PREFIX IS ADDED TO THE CATALOG NUMBER TO DESIGNATE THE REQUIRED FITTINGS AS SHOWN IN THE TABULATION (EXAMPLE: P1530CC):

"P" - REPLACE "S" PREFIX WITH "P" FOR FACTORY INHIBITED AND BAGGED

230417029563	04/17/23	SAV	SI	SP
EC #	DATE	CHANGED BY	CHECKED BY	APPROVED BY
DESCRIPTION:				WEIGHT, LBS
UPDATED EYEBOLT HARDWARE SIZE				SEE TABLE
ADDED S1545CC CATALOG				
ADDITIONAL COMMENTS: --				

THIRD ANGLE PROJECTION

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS

HUBBELL POWER SYSTEMS, Inc.

TITLE: **S15XX CLAMP, HOT LINE, CU**

CATALOG NUMBER: **SEE TABLE**

SIZE	DWG NO.	PART / ASSY NO.	REV
C	CC-25762	SEE TABLE	2

SCALE: 1 : 1 DRN BY: SD DATE: 10/22/18 SHEET 1 OF 1

WI-ENG-142 - 111020-R1

4

3

2

1