






LINE TERMINAL DETAIL



HDG 4-HOLE TERMINAL PAD, PART No. 274914-4002

GROUND TERMINAL DETAIL



HDG 4-HOLE TERMINAL PAD, PART No. 274914-4001

Ø = DIAMETER
HDG = HOT DIP GALVANIZED

CHARACTERISTICS

RATED VOLTAGE (Ur)	96 kVrms
MCOV (Uc)	76 kVrms
MASS	26.7 kg (58.9 lb)
COG ABOVE BASE	589 (23.2)
CREEPAGE DISTANCE	3124 (123)
STRIKE DISTANCE	1100 (43.3)
LIGHTNING IMP W/S	631 kVpk
SWITCHING IMP WET W/S	529 kVpk
POWER FREQ WET W/S	275 kVrms
TOV 1s NO PRIOR DUTY	111 kVrms
TOV 10s NO PRIOR DUTY	106 kVrms
TOV 1s W/PRIOR DUTY	106 kVrms
TOV 10s W/PRIOR DUTY	100 kVrms

CANTILEVER FORCE

MAXIMUM CONTINUOUS	897 N (202 lbf)
ULTIMATE (max pk)	1794 N (403 lbf)

RECOMMENDED CLEARANCE (METAL - METAL)

PHASE TO GROUND	441.4 (17.4)
PHASE TO PHASE	512.6 (20.2)

NOTES:

1. DIMENSIONS IN millimeters(inches) SUBJECT TO ±3% TOLERANCE
2. CLEARANCE AND INSULATION W/S VOLTAGE APPLY AT SEA LEVEL
3. ARRESTER SUITABLE FOR OPERATION AT ALTITUDES UP TO 4380 m (14370 ft)
4. PACKAGED IN A CORRUGATED BOX.

.5μSEC 10kA IR kV	SWITCHING SURGE IR kV		MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
	500 A	1 KA	1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
257	184	191	196	206	216	232	251	286

IEEE C62.11

STATION-CLASS
SURGE ARRESTER

Program Revision
2015.07.30.08.09.10

REV DATE
05/03/11

CONFIDENTIAL: THIS DRAWING AND ITS
CONTENTS ARE CONFIDENTIAL AND THE
EXCLUSIVE PROPERTY OF HUBBELL
POWER SYSTEMS. NO PUBLICATION,
DISTRIBUTION OR COPIES MAY BE MADE
WITHOUT THE WRITTEN CONSENT OF
HUBBELL POWER SYSTEMS. UNPUBLISHED
ALL RIGHTS RESERVED UNDER THE
COPYRIGHT LAWS.

TITLE

**EVP ARRESTER
76 KV MCOV**

SIZE

S

DWG NO.

191064520

CAT / PART / ASSY NO.

EVP0076003012

REV

1

DO NOT SCALE
THIS DRAWING

DRN BY NON

DATE 05/03/11

SHEET 1 OF 1



HUBBELL POWER SYSTEMS